



Customer information packet

L1319-50

1.5/1.1KW, 1460RPM, 1PH, 50HZ, 56, 3540LC, OPE

Class - None

Division - Not Applicable

Specifications

Enclosure	OPEN
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.100 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	220.0 V @ 50 HZ
Agency Approvals	C UR US WEEE UKCA CURUS CE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.200 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.2 a

Part detail

Revision	F
Type	AC
Mech. spec.	35M497
Base	
Status	PRD/A
Elec. spec.	35WGG775
Layout	35LYM497
Eff. date	02-13-2025
CD Diagram	CD0017A02
Poles	04
Leads	4#18
Proprietary	False
Created date	05-26-2023

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Finish	CLEAR COAT
Motor Lead Quantity/Wire Size	4 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3540LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.32 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1460 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L									
CAT.NO.	L1319-50								
SPEC.	35M497G775								
HP	1.5/1.1KW								
VOLTS	220								
AMP	6.2								
R.P.M. (1/MIN)	1460								
FRAME	56		HZ	50			PH	1	
SER.F.	1.00	CODE	J	DES	-	CL	F		
NEMA-NOM-EFF	81.4	PF	98						
RATING	40C AMB-S1 CONT								
CC			IP22 KG27 IC01						
DE	6205		ODE	6203					
ENCL	OPEN	SN							

Accessories

Part number	Description	Multiplier
35-8764	C FACE KIT	A8
35EP1604A01SP	D-FLANGE KIT	

AC Induction Motor Performance Data

Record # 101572

Typical performance - not guaranteed values

Winding: 35WGG775-R001			Type: 3540LC		Enclosure: OPEN	
Nameplate Data			220 V, 50 Hz: Single Voltage Motor			
Rated Output (KW)		1.1	Full Load Torque		5.363 LB-FT	
Volts		220	Start Configuration		direct on line	
Full Load Amps		6.2	Breakdown Torque		15.2 LB-FT	
R.P.M.		1450	Pull-up Torque		11.8 LB-FT	
Hz	50	Phase	1	Locked-rotor Torque	15 LB-FT	
NEMA Design Code		- KVA Code	J	Starting Current	48.9 A	
Service Factor (S.F.)			1	No-load Current	1.47 A	
NEMA Nom. Eff.	81.4	Power Factor	98	Line-line Res. @ 25°C	1.8543 Ω A Ph 2.5899 Ω B Ph	
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load	55°C	

Load Characteristics 220 V, 50 Hz, 1.1 KW

% of Rated Load	25	50	75	100	125	150
Power Factor	93	97	98	98	98	98
Efficiency	60.7	76.9	81.6	82.9	81.7	79
Speed	1488	1478.5	1467.8	1455.5	1441.3	1422.5
Line amperes	2.23	3.35	4.73	6.19	7.82	9.7


ABB Motors and Mechanical Inc.


WINDING # 35WGG775

Typical performance - not guaranteed values.


1.1 KW 1 PH 50 HZ 1450 RPM 220 V 3540LC

TORQUES (LB-FT): PO=15.2 PU=11.8 LR=15 LRA=48.9





CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

- NOTES:
- 1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
 - 2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
 - 3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, SV, REV, 4 LEADS

CD0017A02