

BALDOR • RELIANCE

Customer information packet

L3709T

7.5HP, 3450RPM, 1PH, 60HZ, 213T, 3735LC, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	7.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	33.000 A @ 230.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	83.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	33.0 a
Insulation Class	F
Inverter Code	Not Inverter

Part detail

Revision	L
Type	AC
Mech. spec.	37M324
Base	
Status	PRD/A
Elec. spec.	37WGW579
Layout	37LYM324
Eff. date	05-13-2024
CD Diagram	CD0017A02
Poles	02
Leads	2#10 A PH,2#14 B PH
Proprietary	False
Created date	02-11-2010

KVA Code	F
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 10 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3735LC
Mounting Arrangement	F1
Number of Poles	2
Overall Length	17.89 IN
Power Factor	91
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	L3709T								
SPEC.	37M324W579G1								
HP	7.5								
VOLTS	230								
AMP	33								
RPM	3450								
FRAME	213T		HZ	60		PH	1		
SER.F.	1.00	CODE	F	DES	L	CLASS	F		
NEMA-NOM-EFF	83	PF	91						
RATING	40C AMB-CONT								
CC									
DE	6307		ODE	6206					
ENCL	TEFC	SN							

Accessories

Part number	Description	Multiplier
37-3301	C FACE KIT	P1

AC Induction Motor Performance Data

Record # 61322

Typical performance - not guaranteed values

Winding: 37GWG579-R002		Type: 3735LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	7.5	Full Load Torque	11.2 LB-FT		
Volts	230	Start Configuration	direct on line		
Full Load Amps	33	Breakdown Torque	35 LB-FT		
R.P.M.	3450	Pull-up Torque	17 LB-FT		
Hz	60 Phase	1	Locked-rotor Torque	28 LB-FT	
NEMA Design Code	L	KVA Code	F	Starting Current	220 A
Service Factor (S.F.)		1	No-load Current	8.2 A	
NEMA Nom. Eff.	83	Power Factor	91	Line-line Res. @ 25°C	0.22 Ω A Ph 0.98 Ω B Ph
Rating - Duty		40C	AMB-CONT	Temp. Rise @ Rated Load	88°C

Load Characteristics 230 V, 60 Hz, 7.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	76	88	92	94	94	94
Efficiency	66.7	78.4	82.2	83.3	82.9	81.6
Speed	3575	3555	3533	3508	3481	3449
Line amperes	12	17.6	24.1	31.2	39	47.6


ABB Motors and Mechanical Inc.


WINDING # 37WGW579

Typical performance - not guaranteed values.


7.5 HP 1 PH 60 HZ 3450 RPM 230 V 3735LC

TORQUES (LB-FT): PO=35 PU=17 LR=28 LRA=220





CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0017A02

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, SV, REV, 4 LEADS