



Customer information packet

EMVM3559C

2.2KW, 3450RPM, 3PH, 60HZ, D90LC, 3532M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	D90LC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	2.200 KW @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA EEV CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.600 A @ 460.0 V 7.200 A @ 230.0 V 7.900 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Frame Prefix	D

Part detail

Revision	M
Type	AC
Mech. spec.	35S714
Base	
Status	PRD/A
Elec. spec.	35WGQ060
Layout	35LYS714
Eff. date	04-30-2024
CD Diagram	CD0005
Poles	02
Leads	9#18
Proprietary	False
Created date	05-06-2015

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	3.6 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Motor Type	3532M
Mounting Arrangement	B14
Number of Poles	2
Overall Length	14.63 IN
Power Factor	92
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.945 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP3386L						
CAT.NO.	EMVM3559C					
SPEC.	35S714Q060G2					
IEC FRAME	D90SC,LC	KW	2.2			
VOLTS	230/460					
AMP	7.2/3.6					
RPM	3450		ENCL		TEFC	
HZ	60	PH	3	CL	F	
SER.F.	1.15	DES	B	CODE	L	
NEMA-NOM-EFF	86.5	I.P.	44			
RATING	40C AMB-CONT					
CC	010A	USABLE AT 208V				N/A
DE	6206	ODE	6203			
SER. #						

AC Induction Motor Performance Data

Record # 61529

Typical performance - not guaranteed values

Winding: 35WGQ060-R022			Type: 3532M		Enclosure: TEFC		
Nameplate Data			460 V, 60 Hz: High Voltage Connection				
Rated Output (KW)		2.2	Full Load Torque		4.61 LB-FT		
Volts		230/460	Start Configuration		direct on line		
Full Load Amps		7.2/3.6	Breakdown Torque		19.9 LB-FT		
R.P.M.		3450	Pull-up Torque		11.9 LB-FT		
Hz	60	Phase	3	Locked-rotor Torque		18.8 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		33.1 A
Service Factor (S.F.)		1.15	No-load Current		1.17 A		
NEMA Nom. Eff.		86.5	Power Factor	92	Line-line Res. @ 25°C		4.7916 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		57°C
S.F. Amps					Temp. Rise @ S.F. Load		72°C

Load Characteristics 460 V, 60 Hz, 2.2 KW

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	62	81	88	92	93	94	93
Efficiency	83.7	87.9	88.2	87.2	85.6	83.5	86.2
Speed	3562.2	3530.9	3497.8	3462.5	3420.8	3375.4	3437
Line amperes	1.5	2.08	2.79	3.57	4.46	5.44	4.1

ABB Motors and Mechanical Inc.

WINDING # 35WGQ060

Typical performance - not guaranteed values.

2.2 KW 3 PH 60 HZ 3450 RPM 460 V 3532M

TORQUES (LB-FT): PO=19.9 PU=11.9 LR=18.8 LRA=33.1





