



Customer information packet

M3542-57

.75HP, 1425 IP44RPM, 3PH, 50HZ, 56, 3428M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ 400.0 V @ 50 HZ
Agency Approvals	CE CSA IE2 UR WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.100 A @ 230.0 V 1.800 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

Part detail

Revision	R
Type	AC
Mech. spec.	34A061
Base	
Status	PRD/A
Elec. spec.	34WG3996
Layout	34LYA061
Eff. date	12-30-2024
CD Diagram	CD0022
Poles	04
Leads	6#18
Proprietary	False
Created date	09-08-2011

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.8 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.85 IN
Power Factor	59
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1425 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2717L									
CAT NO	M3542-57								
SPEC.	34A061-3996G1								
HP	.75/KW.56						PH	3	
VOLTS	230/400								
AMP	3.1/1.8								
RPM	1425 1/MIN								
FRAME	56		HZ		50		I.P.		44
SER.F.	1.25	CODE	L	DES	B	CL	F		
NEMA-NOM-EFF	75.5						% (100%)		
PF	59								
RATING	40C AMB-S1 CONT				CC				
DE BRG	6203		ODE		6203				
ENCL	TEFC	SN							
BLANK	SFA 3.5/2								
	KG15 IC411								
	IE2 76.0(75%)69.9(50%)								

AC Induction Motor Performance Data

Record # 35183

Typical performance - not guaranteed values

Winding: 34WG3996-R006			Type: 3428M		Enclosure: TEFC		
Nameplate Data				400 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		.75		Full Load Torque		2.71 LB-FT	
Volts		230/400		Start Configuration		direct on line	
Full Load Amps		3.1/1.8		Breakdown Torque		13.3 LB-FT	
R.P.M.		1425		Pull-up Torque		8.9 LB-FT	
Hz	50	Phase	3	Locked-rotor Torque		9.78 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		10.5 A
Service Factor (S.F.)		1.25		No-load Current		1.4 A	
NEMA Nom. Eff.		75.5	Power Factor	59	Line-line Res. @ 25°C		12.8 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load			
S.F. Amps		3.5/2		Temp. Rise @ S.F. Load			
				Locked-rotor Power Factor		60	
				Rotor inertia		0.0667 LB-FT2	

Load Characteristics 400 V, 50 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	26	39	50	59	67	72	67
Efficiency	55.9	69.9	76	78.5	80.1	80.4	80.1
Speed	1487	1476	1465	1452	1439	1425	1439
Line amperes	1.42	1.49	1.6	1.74	1.9	2.1	1.9


ABB Motors and Mechanical Inc.


WINDING # 34WG3996

Typical performance - not guaranteed values.


0.75 HP 3 PH 50 HZ 1425 RPM 400 V 3428M

TORQUES (LB-FT): PO=13.3 PU=8.9 LR=9.78 LRA=10.5






CD0022




LOW VOLTAGE
(1D)



LINE

HIGH VOLTAGE
(1Y)



LINE

- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS

REV. LTR: F

BY: JLP

REVISED: 01/21/99 3:54

TDR: 0171435

CD0022

FILE: AAA00005144

MDL: -

MTL: -

BALDOR ELECTRIC Co.

3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022