



Customer information packet

MVM3542C

.56KW, 1725RPM, 3PH, 60HZ, D80C, 3420M, TEFC

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	D80C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	3.600 A @ 208.0 V 3.200 A @ 208.0 V 3.000 A @ 230.0 V 1.500 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Frame Prefix	D

Part detail

Revision	AH
Type	AC
Mech. spec.	34G620
Base	
Status	PRD/A
Elec. spec.	34WG0883
Layout	34LYG620
Eff. date	10-25-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-01-0001

Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.5 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	IEC
Motor Type	3420M
Mounting Arrangement	F2
Number of Poles	4
Overall Length	11.11 IN
Power Factor	60
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Tapped & Key
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.748 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None

Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Nameplate

NP1379L									
CAT.NO.	MVM3542C								
SPEC.	34G620-883								
IEC FRAME	D80C	K.W.		.56 TE					
VOLTS	208-230/460								
AMP	3.2-3/1.5								
RPM	1725			I.P.		54			
HZ	60		PH		3	CL		B	K
SER.F.	1.25		DES		B	CODE			
NEMA-NOM-EFF	75.5		PF		60				
RATING	40C AMB-CONT								
CC									
DE	6205	ODE		6203					
SER. #									
	SFA 3.6-3.4/1.7								

AC Induction Motor Performance Data

Record # 6605

Typical performance - not guaranteed values

Winding: 34WG0883-R001			Type: 3420M		Enclosure: TEFC	
Nameplate Data			460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.75	Full Load Torque		2.25 LB-FT	
Volts		208-230/460	Start Configuration		direct on line	
Full Load Amps		3.2-3/1.5	Breakdown Torque		10 LB-FT	
R.P.M.		1725	Pull-up Torque		8.5 LB-FT	
Hz		60	Phase		3	
NEMA Design Code		B	KVA Code		K	
Service Factor (S.F.)		1.25	Starting Current		10 A	
NEMA Nom. Eff.		75.5	Power Factor		60	
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load	
S.F. Amps		3.6-3.4/1.7	Temp. Rise @ S.F. Load		87°C	
			Locked-rotor Power Factor		57.5	
			Rotor inertia		0.0476 LB-FT2	

Load Characteristics 460 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	27	42	54	61	70	75	71
Efficiency	56.1	70	74.8	76.2	76	75.3	76.1
Speed	1783	1766	1749	1731	1711	1693	1711
Line amperes	1.2	1.2	1.3	1.5	1.6	1.8	1.6


ABB Motors and Mechanical Inc.


WINDING # 34WG0883

Typical performance - not guaranteed values.




0.75 HP 3 PH 60 HZ 1725 RPM 460 V 3420M

TORQUES (LB-FT): PO=10 PU=8.5 LR=8.8 LRA=10





CD0005



- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
900000		FILE: AAA00005140	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 9 LEADS

CD0005