

# Universal crop dryer, single phase, PSC (switchless), OPAO

5 thru 15 Hp

**IP22**



**Features:**

- Shaft length 3/4" longer than NEMA standard
- 1/4-20 tapped and keyed shaft
- Convenient lead location for ease of conduit connectivity
- Switchless design for increased reliability
- Lubed for life double shielded ball bearings
- Normally closed winding thermostats to protect against overheating

**Applications:**

- Vane axial fan crop dryers

Hp	RPM	NEMA Frame	Catalog Number	List Price	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>Open air over</b>											
5 - 7.5	3600	184TZ	<b>UCC5700</b>	1,894	FD1	15.38	74	79	230	19.5	
7.5 - 10	3600	184TZ	<b>UCC7100</b>	2,081	FD1	16.88	78	85.5	230	28	
10 - 15	3600	215Z	<b>UCC10150</b>	3,934	FD1	18.57	127	83	230	41	

(a) See notes on inside back flap.

Information

General purpose Single phase

General purpose Three phase

Severe duty

Large Motors and Generators

Washdown duty

Explosion proof

Pump

HVAC

Farm duty