

BALDOR • RELIANCE

Customer information packet

VEBM3546T-5

1HP, 1774RPM, 3PH, 60HZ, 143TC, 3522M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

| | |
|--------------------------------|---------------------------|
| Enclosure | TEFC |
| Frame | 143TC |
| Frame Material | Steel |
| Frequency | 60.00 Hz |
| Haz Area Class and Group | None |
| Haz Area Division | Not Applicable |
| Motor Letter Type | Three Phase |
| Output @ Frequency | 1.000 HP @ 60 HZ |
| Phase | 3 |
| Synchronous Speed @ Frequency | 1800 RPM @ 60 HZ |
| Voltage @ Frequency | 575.0 V @ 60 HZ |
| Agency Approvals | CURUSEEV NEMA PREMIUM |
| Ambient Temperature | 40 °C |
| Auxillary Box | No Auxillary Box |
| Auxillary Box Lead Termination | None |
| Base Indicator | No Mounting |
| Bearing Grease Type | Polyrex EM (-20F +300F) |
| Blower | None |
| Current @ Voltage | 1.300 A @ 575.0 V |
| Design Code | B |
| Drip Cover | No Drip Cover |
| Duty Rating | CONT |
| Efficiency @ 100% Load | 85.5 % |
| Electrically Isolated Bearing | Not Electrically Isolated |
| Feedback Device | NO FEEDBACK |
| Front Shaft Indicator | None |
| Heater Indicator | No Heater |
| High Voltage Full Load Amps | 1.3 a |
| Insulation Class | F |
| Inverter Code | Inverter Ready |
| KVA Code | M |

Part detail

| | |
|--------------|------------|
| Revision | H |
| Type | AC |
| Mech. spec. | 35E060 |
| Base | |
| Status | PRD/A |
| Elec. spec. | 35WGG119 |
| Layout | 35LYE060 |
| Eff. date | 12-18-2024 |
| CD Diagram | CD0006 |
| Poles | 04 |
| Leads | 3#18 |
| Proprietary | False |
| Created date | 01-10-2022 |

| | |
|--------------------------------------|---------------------|
| Lifting Lugs | No Lifting Lugs |
| Locked Bearing Indicator | Locked Bearing |
| Motor Lead Quantity/Wire Size | 3 @ 18 AWG |
| Motor Lead Termination | Flying Leads |
| Motor Standards | NEMA |
| Motor Type | 3522M |
| Mounting Arrangement | F1 |
| Number of Poles | 4 |
| Overall Length | 17.87 IN |
| Power Factor | 70 |
| Product Family | General Purpose |
| Pulley End Bearing Type | Ball |
| Pulley Face Code | C-Face |
| Pulley Shaft Indicator | Standard |
| Rodent Screen | None |
| Service Factor | 1.15 |
| Shaft Diameter | 0.875 IN |
| Shaft Ground Indicator | No Shaft Grounding |
| Shaft Rotation | Reversible |
| Shaft Slinger Indicator | No Slinger |
| Speed | 1775 rpm |
| Speed Code | Single Speed |
| Starting Method | Direct on line |
| Thermal Device - Bearing | None |
| Thermal Device - Winding | None |
| Vibration Sensor Indicator | No Vibration Sensor |
| Winding Thermal 1 | None |
| Winding Thermal 2 | None |

Nameplate

| NP1259L | | | | | | | | | |
|---------------------|--------------|-------------|------------|------------|---|-----------|---|--|--|
| CAT.NO. | VEBM3546T-5 | | | | | | | | |
| SPEC. | 35E060G119G1 | | | | | | | | |
| HP | 1 | | | | | | | | |
| VOLTS | 575 | | | | | | | | |
| AMP | 1.3 | | | | | | | | |
| RPM | 1775 | | | | | | | | |
| FRAME | 143TC | | HZ | 60 | | PH | 3 | | |
| SER.F. | 1.15 | CODE | M | DES | B | CL | F | | |
| NEMA-NOM-EFF | 85.5 | PF | 70 | | | | | | |
| RATING | 40C AMB-CONT | | | | | | | | |
| CC | 010A | | | | | | | | |
| DE | 6205 | | ODE | 6203 | | | | | |
| ENCL | TEFC | SN | | | | | | | |
| | SFA 1.4 | | | | | | | | |

AC Induction Motor Performance Data

Record # 99012

Typical performance - not guaranteed values

| Winding: 35WGG119-R001 | | Type: 3522M | | Enclosure: TEFC | |
|-------------------------------|------|----------------------------------|---|------------------------|--|
| Nameplate Data | | | 575 V, 60 Hz: Single Voltage Motor | | |
| Rated Output (HP) | 1 | Full Load Torque | 2.99 LB-FT | | |
| Volts | 575 | Start Configuration | direct on line | | |
| Full Load Amps | 1.3 | Breakdown Torque | 13.4 LB-FT | | |
| R.P.M. | 1775 | Pull-up Torque | 6.8 LB-FT | | |
| Hz | 60 | Locked-rotor Torque | 8.3 LB-FT | | |
| NEMA Design Code | B | Starting Current | 10.9 A | | |
| Service Factor (S.F.) | 1.15 | No-load Current | 0.87 A | | |
| NEMA Nom. Eff. | 85.5 | Line-line Res. @ 25°C | 30.1 Ω | | |
| Rating - Duty | 40C | Temp. Rise @ Rated Load | 36°C | | |
| S.F. Amps | 1.4 | Temp. Rise @ S.F. Load | 42°C | | |
| | | Locked-rotor Power Factor | 63.4 | | |
| | | Rotor inertia | 0.159 lb-ft ² | | |

Load Characteristics 575 V, 60 Hz, 1 HP

| % of Rated Load | 25 | 50 | 75 | 100 | 125 | 150 | S.F. |
|------------------------|-----------|-----------|-----------|------------|------------|------------|-------------|
| Power Factor | 31 | 48 | 61 | 70 | 76 | 80 | 74 |
| Efficiency | 72.1 | 81.6 | 84.9 | 85.8 | 85.7 | 85 | 85.7 |
| Speed | 1794 | 1787 | 1781 | 1774 | 1767 | 1758 | 1770 |
| Line amperes | 0.89 | 0.97 | 1.1 | 1.26 | 1.44 | 1.65 | 1.37 |


ABB Motors and Mechanical Inc.

WINDING # 35WGG119


1 HP 3 PH 60 HZ 1775 RPM 575 V 3522M

Typical performance - not guaranteed values.


TORQUES (LB-FT): PO=13.4 PU=6.8 LR=8.3 LRA=10.9



6/9/2025 ACPERF, record # 99012



CD0006



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

| | | |
|-----------------------------------|------------------------------|-------------------|
| REV. DESC: ADD CLASS CONN00000007 | | |
| REV. LTR: E | VERSION: 01 | TDR: 000001099922 |
| FILE: \AAA\00005\141 | REVISED: 10:24:49 02/19/2019 | BY: ENBRIRO |
| MTL: - | © □ | |

BALDOR - RELIANCE®

3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED

SH 1 of 1