



Customer information packet

KM3454-57

.25HP, IP54, 1425RPM, 3PH, 50HZ, 56C, 3410M

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.250 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	400.0 V @ 50 HZ 230.0 V @ 50 HZ
Agency Approvals	CE CSA UR WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.700 A @ 400.0 V 1.200 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	64.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part detail

Revision	Q
Type	AC
Mech. spec.	34A063
Base	
Status	PRD/A
Elec. spec.	34WGS886
Layout	34LYA063
Eff. date	02-10-2025
CD Diagram	CD0022
Poles	04
Leads	6#18
Proprietary	False
Created date	09-02-2011

Heater Indicator	No Heater
High Voltage Full Load Amps	0.7 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3410M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	11.35 IN
Power Factor	59
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1425 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor

Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L									
CAT.NO.	KM3454-57								
SPEC.	34A063S886G1								
HP	.25/KW .18								
VOLTS	230/400								
AMP	1.2/.7 SFA 1.3/.75								
R.P.M. (1/MIN)	1425								
FRAME	56C		HZ	50			PH	3	
SER.F.	1.25	CODE		L	DES	B	CL	B	
NEMA-NOM-EFF	64	PF		59					
RATING	40C AMB-S1 CONT								
CC			IP44 KG9 IC411						
DE	6203		ODE		6203				
ENCL	TEFC	SN							
	IE2-61.9(75%)53.7(50%)								

AC Induction Motor Performance Data

Record # 35108

Typical performance - not guaranteed values

Winding: 34WGS886-R001				Type: 3410M		Enclosure: TEFC	
Nameplate Data				400 V, 50 Hz: High Voltage Connection			
Rated Output (HP)		.25		Full Load Torque		0.901 LB-FT	
Volts		230/400		Start Configuration		direct on line	
Full Load Amps		1.2/.7		Breakdown Torque		2.93 LB-FT	
R.P.M.		1425		Pull-up Torque		1.97 LB-FT	
Hz	50	Phase	3	Locked-rotor Torque		2.16 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		2.75 A
Service Factor (S.F.)		1.25		No-load Current		0.59 A	
NEMA Nom. Eff.		64	Power Factor	59	Line-line Res. @ 25°C		72 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		53°C	
S.F. Amps		1.3/.75		Temp. Rise @ S.F. Load		60°C	
				Locked-rotor Power Factor		80	
				Rotor inertia		0.0238 LB-FT2	

Load Characteristics 400 V, 50 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	42	51	59	67	74	67
Efficiency	37.9	53.7	61.9	66.1	68.2	68.2	68.2
Speed	1483	1470	1456	1440	1423	1404	1423
Line amperes	0.592	0.603	0.635	0.678	0.723	0.769	0.723


ABB Motors and Mechanical Inc.

WINDING # 34WGS886

Typical performance - not guaranteed values.

0.25 HP 3 PH 50 HZ 1425 RPM 400 V 3410M

TORQUES (LB-FT): PO=2.93 PU=1.97 LR=2.16 LRA=2.75



AC Induction Motor Performance Data

Record # 46459

Typical performance - not guaranteed values

Winding: 34WGS886-R001			Type: 3410M		Enclosure: TEFC		
Nameplate Data				230 V, 50 Hz: Low Voltage Connection			
Rated Output (HP)		.25		Full Load Torque		0.901 LB-FT	
Volts		230/400		Start Configuration		direct on line	
Full Load Amps		1.2/.7		Breakdown Torque		2.91 LB-FT	
R.P.M.		1425		Pull-up Torque		1.95 LB-FT	
Hz	50	Phase	3	Locked-rotor Torque		2.14 LB-FT	
NEMA Design Code		B	KVA Code	L	Starting Current		4.74 A
Service Factor (S.F.)		1.25		No-load Current		1.01 A	
NEMA Nom. Eff.		64	Power Factor	59	Line-line Res. @ 25°C		24.1 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		52°C	
S.F. Amps		1.3/.75		Temp. Rise @ S.F. Load		59°C	
				Locked-rotor Power Factor		80	
				Rotor inertia		0.0238 LB-FT2	

Load Characteristics 230 V, 50 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	30	42	52	60	68	74	68
Efficiency	38.4	54.1	62.3	66.3	68.4	68.3	68.4
Speed	1483	1470	1456	1440	1422	1403	1422
Line amperes	1.02	1.04	1.09	1.17	1.24	1.33	1.24


ABB Motors and Mechanical Inc.


WINDING # 34WGS886

Typical performance - not guaranteed values.


0.25 HP 3 PH 50 HZ 1425 RPM 230 V 3410M

TORQUES (LB-FT) : PO=2.91 PU=1.95 LR=2.14 LRA=4.74






CD0022




LOW VOLTAGE
(1D)



LINE

HIGH VOLTAGE
(1Y)



LINE

- NOTES:
- 1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
 - 2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
 - 3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
 - 4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022