

**BALDOR® • RELIANCE™**

---

# Customer information packet

## L3605T-50

2/1.5KW, 1460RPM, 1PH, 50HZ, 182T, 3646LC, TEF

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	182T
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	110.0 V @ 50 HZ 220.0 V @ 50 HZ
Agency Approvals	C UR US CE CURUS UKCA WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.200 A @ 220.0 V 18.400 A @ 110.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	82.8 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

## Part detail

Revision	G
Type	AC
Mech. spec.	36E004
Base	
Status	PRD/A
Elec. spec.	36WGQ056
Layout	36LYE004
Eff. date	05-05-2025
CD Diagram	CD0055
Poles	04
Leads	4#14 A PH,2#16 B PH
Proprietary	False
Created date	03-07-2023

Heater Indicator	No Heater
High Voltage Full Load Amps	9.2 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	4 @ 14 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3646LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.06 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1460 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

<b>NP1372L</b>										
<b>CAT.NO.</b>	L3605T-50									
<b>SPEC.</b>	36E004Q056									
<b>HP</b>	2/1.5KW									
<b>VOLTS</b>	110/220									
<b>AMP</b>	18.4/9.2									
<b>R.P.M. (1/MIN)</b>	1460									
<b>FRAME</b>	182T		<b>HZ</b>	50		<b>PH</b>	1			
<b>SER.F.</b>	1.15	<b>CODE</b>	K	<b>DES</b>	-	<b>CL</b>	F			
<b>NEMA-NOM-EFF</b>	82.8	<b>PF</b>	90							
<b>RATING</b>	40C AMB-S1 CONT									
<b>CC</b>			IP44 IC410 45KG							
<b>DE</b>	6206		<b>ODE</b>	6205						
<b>ENCL</b>	TEFC	<b>SN</b>								
	IE2-50HZ 83 (75%),82 (50%)									

**Accessories**

<b>Part number</b>	<b>Description</b>	<b>Multiplier</b>
36-3301	C FACE KIT	A8
36EP1304A62SP	FLANGE MTD ENDPLATE 182-4TD -ENCL (LESS	A8

**AC Induction Motor Performance Data**

Record # 101574

Typical performance - not guaranteed values

Winding: 36WGQ056-R001		Type: 3646LC	Enclosure: TEFC	
<b>Nameplate Data</b>			<b>220 V, 50 Hz: High Voltage Connection</b>	
Rated Output (KW)	1.5	Full Load Torque	7.229 LB-FT	
Volts	110/220	Start Configuration	direct on line	
Full Load Amps	18.4/9.2	Breakdown Torque	19.6 LB-FT	
R.P.M.	1460	Pull-up Torque	11.6 LB-FT	
Hz	50 Phase	1	Locked-rotor Torque	24.3 LB-FT
NEMA Design Code	- KVA Code	K	Starting Current	72.7 A
Service Factor (S.F.)	1.15	No-load Current	2.9 A	
NEMA Nom. Eff.	82.8 Power Factor	90	Line-line Res. @ 25°C	0.85625 Ω A Ph 0.80862 Ω B Ph
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	37°C	
S.F. Amps		Temp. Rise @ S.F. Load	47°C	

**Load Characteristics 220 V, 50 Hz, 1.5 KW**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	64	80	87	90	91	91	91
Efficiency	74	82.4	84	83.2	81.1	78	81.9
Speed	1491.1	1482.5	1472.8	1461.6	1448.5	1433.4	1454
Line amperes	3.65	5.17	7.03	9.15	11.6	14.3	10.6


ABB Motors and Mechanical Inc.

WINDING # 36WGQ056


Typical performance - not guaranteed values.

1.5 KW 1 PH 50 HZ 1460 RPM 220 V 3646LC


TORQUES (LB-FT): PO=19.6 PU=11.6 LR=24.3 LRA=72.7



6/9/2025 ACPERF, record # 101574



CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	-
LOW OPP	1,3,5	2,4,8	-

**NOTES:**

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
C00000		FILE: AAA00007414	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

TYPE LC, DV, REV, 6 LEADS