

BALDOR • RELIANCE

Customer information packet

L3912T

15HP, 1770RPM, 1PH, 60HZ, 256T, 3956LC, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	256T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	15.000 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	208.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	58.000 A @ 230.0 V 65.000 A @ 208.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	86.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	58.0 a

Part detail

Revision	R
Type	AC
Mech. spec.	39T044
Base	
Status	PRD/A
Elec. spec.	39WGX905
Layout	39LYT044
Eff. date	02-08-2024
CD Diagram	CD1084
Poles	04
Leads	2#6 A PH, 2#12 B PH
Proprietary	False
Created date	03-12-2015

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	E
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	2 @ 6 AWG, A PH
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3956LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	24.56 IN
Power Factor	96
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1720 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	L3912T								
SPEC.	39T044X905								
HP	15								
VOLTS	208-230								
AMP	65-58								
RPM	1720								
FRAME	256T		HZ	60		PH	1		
SER.F.	1.00	CODE	E	DES	L	CLASS	F		
NEMA-NOM-EFF	86.5	PF	96						
RATING	40C AMB-CONT								
CC									
DE	6309		ODE	6307					
ENCL	TEFC	SN							

AC Induction Motor Performance Data

Record # 59422

Typical performance - not guaranteed values

Winding: 39WGX905-R001		Type: 3956LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: Single Voltage Motor		
Rated Output (HP)	15	Full Load Torque	45.6 LB-FT		
Volts	208-230	Start Configuration	direct on line		
Full Load Amps	65-58	Breakdown Torque	111 LB-FT		
R.P.M.	1720	Pull-up Torque	54.2 LB-FT		
Hz	60 Phase	1	Locked-rotor Torque	93.6 LB-FT	
NEMA Design Code	L KVA Code	E	Starting Current	311 A	
Service Factor (S.F.)		1	No-load Current	4.94 A	
NEMA Nom. Eff.	86.5 Power Factor	96	Line-line Res. @ 25°C	0.12074 Ω A Ph 0.37139 Ω B Ph	
Rating - Duty	40C AMB-CONT		Temp. Rise @ Rated Load	100°C	

Load Characteristics 230 V, 60 Hz, 15 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	96	98	98	97	96	94
Efficiency	81	88.4	88.8	87	83.5	78.8
Speed	1783.3	1766.1	1746.3	1722.4	1693	1654.6
Line amperes	15.7	28	42	57.5	75.3	97.3


ABB Motors and Mechanical Inc.

WINDING # 39WGX905


Typical performance - not guaranteed values.

15 HP 1 PH 60 HZ 1720 RPM 230 V 3956LC


TORQUES (LB-FT): PO=111 PU=54.2 LR=93.6 LRA=311



6/9/2025 ACPERF, record # 59422



CD1084



REV. DESC: NO CHANGES MADE		
REV. LTR: D	VERSION: 01	TDR: 000001193788
FILE: \AAA\00029\485	REVISED: 10:01:49 07/13/2022	BY: ENBRIRO
MTL: -		

BALDOR - RELIANCE®

TYPE LC, SV, REV, 4LD, RELAY W/CENT SW, ON/OFF SW

SH 1 of 1

CD1084