

BALDOR • RELIANCE

Customer information packet

VL3507

.75HP, 1725RPM, 1PH, 60HZ, 56C, 3428LC, TEFC, F

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.750 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	115.0 V @ 60 HZ 230.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	4.200 A @ 230.0 V 4.400 A @ 208.0 V 8.400 A @ 115.0 V
Design Code	N
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	72.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	4.2 a

Part detail

Revision	F
Type	AC
Mech. spec.	34G452
Base	
Status	PRD/A
Elec. spec.	34WGR714
Layout	34LYG452
Eff. date	02-11-2025
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	11-19-2020

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3428LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	12.47 IN
Power Factor	78
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	VL3507								
SPEC.	34G452R714								
HP	.75								
VOLTS	115/230								
AMP	8.4/4.2								
RPM	1725								
FRAME	56C		HZ	60		PH	1		
SER.F.	1.25	CODE	J	DES	N	CLASS	F		
NEMA-NOM-EFF	72	PF	78						
RATING	40C AMB-CONT								
CC									
DE	6203	ODE	6203						
ENCL	TEFC	SN							
	SFA 10/5								

AC Induction Motor Performance Data

Record # 85524

Typical performance - not guaranteed values

Winding: 34WGR714-R001		Type: 3428LC		Enclosure: TEFC	
Nameplate Data			230 V, 60 Hz: High Voltage Connection		
Rated Output (HP)	.75	Full Load Torque	2.25 LB-FT		
Volts	115/230	Start Configuration	direct on line		
Full Load Amps	8.4/4.2	Breakdown Torque	5.4 LB-FT		
R.P.M.	1725	Pull-up Torque	5.1 LB-FT		
Hz	60	Phase	1	Locked-rotor Torque	7.04 LB-FT
NEMA Design Code	N	KVA Code	J	Starting Current	24.54 A
Service Factor (S.F.)	1.25	No-load Current	2.39 A		
NEMA Nom. Eff.	72	Power Factor	78	Line-line Res. @ 25°C	0.726 Ω A Ph 3.03 Ω B Ph
Rating - Duty	40C	AMB-CONT	Temp. Rise @ Rated Load 66°C		
S.F. Amps	10/5	Temp. Rise @ S.F. Load 84°C			Locked-rotor Power Factor 83
			Rotor inertia 0.0665 lb-ft ²		

Load Characteristics 230 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	46	62	73	80	83	83	83
Efficiency	52.6	68.4	72.5	73.5	73	69.2	73
Speed	1780	1765	1747	1727	1704	1670	1704
Line amperes	2.54	2.9	3.45	4.09	4.92	6.06	4.92


ABB Motors and Mechanical Inc.

WINDING # 34WGR714

Typical performance - not guaranteed values.

0.75 HP 1 PH 60 HZ 1725 RPM 230 V 3428LC

TORQUES (LB-FT): PO=5.4 PU=5.1 LR=7.04 LRA=24.54



6/9/2025 ACPERF, record # 85524

AC Induction Motor Performance Data

Record # 85532

Typical performance - not guaranteed values

Winding: 34WGR714-R001		Type: 3428LC	Enclosure: TEFC	
Nameplate Data			115 V, 60 Hz: Low Voltage Connection	
Rated Output (HP)	.75	Full Load Torque	2.26 LB-FT	
Volts	115/230	Start Configuration	direct on line	
Full Load Amps	8.4/4.2	Breakdown Torque	5.41 LB-FT	
R.P.M.	1725	Pull-up Torque	5.31 LB-FT	
Hz	60 Phase	1	Locked-rotor Torque	7.32 LB-FT
NEMA Design Code	N KVA Code	J	Starting Current	47.96 A
Service Factor (S.F.)	1.25	No-load Current	4.78 A	
NEMA Nom. Eff.	72 Power Factor	78	Line-line Res. @ 25°C	0.726 Ω A Ph 3.03 Ω B Ph
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	66°C	
S.F. Amps	10/5	Temp. Rise @ S.F. Load	82°C	
		Locked-rotor Power Factor	85.8	
		Rotor inertia	0.0665 lb-ft ²	

Load Characteristics 115 V, 60 Hz, 0.75 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	46	62	73	80	83	84	83
Efficiency	52.7	68.4	72.5	73.6	72.8	69	72.8
Speed	1780	1765	1747	1726	1703	1670	1703
Line amperes	5.07	5.78	6.88	8.16	9.82	12.09	9.82


ABB Motors and Mechanical Inc.


WINDING # 34WGR714

Typical performance - not guaranteed values.


0.75 HP 1 PH 60 HZ 1725 RPM 115 V 3428LC

TORQUES (LB-FT): PO=5.41 PU=5.31 LR=7.32 LRA=47.96





CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	-
LOW OPP	1,3,5	2,4,8	-

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
C00000		FILE: AAA00007414	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, DV, REV, 6 LEADS