

**BALDOR • RELIANCE**

---

# Customer information packet

## VL3510-50

1/.75KW, 1450RPM, 1PH, 50HZ, 56C, 3532LC, TEFC

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	.750 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	110.0 V @ 50 HZ 220.0 V @ 50 HZ
Agency Approvals	C UR US CE CURUS UKCA WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	9.200 A @ 110.0 V 4.600 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	79.6 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

## Part detail

Revision	G
Type	AC
Mech. spec.	35E022
Base	
Status	PRD/A
Elec. spec.	35WGG768
Layout	35LYE022
Eff. date	08-13-2024
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	10-10-2023

Heater Indicator	No Heater
High Voltage Full Load Amps	4.6 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.10 IN
Power Factor	92
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

**Nameplate**

<b>NP1372L</b>									
<b>CAT.NO.</b>	VL3510-50								
<b>SPEC.</b>	35E022G768								
<b>HP</b>	1/.75KW								
<b>VOLTS</b>	110/220								
<b>AMP</b>	9.2/4.6								
<b>R.P.M. (1/MIN)</b>	1450								
<b>FRAME</b>	56C		<b>HZ</b>	50		<b>PH</b>	1		
<b>SER.F.</b>	1.15	<b>CODE</b>	K	<b>DES</b>	N	<b>CL</b>	F		
<b>NEMA-NOM-EFF</b>	79.6	<b>PF</b>	92						
<b>RATING</b>	40C AMB-S1 CONT								
<b>CC</b>		IP44 IC411 30KG							
<b>DE</b>	6205	<b>ODE</b>	6203						
<b>ENCL</b>	TEFC	<b>SN</b>							
	IE2-50HZ 79(75%),74(50%)								

**AC Induction Motor Performance Data**

Record # 101540

Typical performance - not guaranteed values

Winding: 35WGG768-R001		Type: 3532LC	Enclosure: TEFC	
<b>Nameplate Data</b>			<b>220 V, 50 Hz: High Voltage Connection</b>	
Rated Output (KW)	.75	Full Load Torque	3.618 LB-FT	
Volts	110/220	Start Configuration	direct on line	
Full Load Amps	9.2/4.6	Breakdown Torque	9.51 LB-FT	
R.P.M.	1450	Pull-up Torque	7.59 LB-FT	
Hz	50 Phase	1	Locked-rotor Torque	8.41 LB-FT
NEMA Design Code	N KVA Code	K	Starting Current	36.6 A
Service Factor (S.F.)	1.15	No-load Current	1.9 A	
NEMA Nom. Eff.	79.6 Power Factor	92	Line-line Res. @ 25°C	2.9253 Ω A Ph 1.7076 Ω B Ph
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load	46°C	
S.F. Amps		Temp. Rise @ S.F. Load	55°C	

**Load Characteristics 220 V, 50 Hz, 0.75 KW**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	64	80	88	92	93	94	93
Efficiency	61	74.9	79.6	80.3	79.2	76.4	79.6
Speed	1488.8	1479.7	1469.4	1458	1444.3	1426.9	1450
Line amperes	2.19	2.84	3.66	4.63	5.74	7.08	5.3


ABB Motors and Mechanical Inc.

WINDING # 35WGG768


Typical performance - not guaranteed values.

0.75 KW 1 PH 50 HZ 1450 RPM 220 V 3532LC


TORQUES (LB-FT): PO=9.51 PU=7.59 LR=8.41 LRA=36.6



6/9/2025 ACPERF, record # 101540



CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	-
LOW OPP	1,3,5	2,4,8	-

**NOTES:**

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
C00000		FILE: AAA00007414	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

TYPE LC, DV, REV, 6 LEADS