



Customer information packet

VM3531

.25HP, 1140RPM, 3PH, 60HZ, 56C, 3411M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.250 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.700 A @ 460.0 V 1.400 A @ 230.0 V 1.600 A @ 208.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	W
Type	AC
Mech. spec.	34A063
Base	
Status	PRD/A
Elec. spec.	34WG5882
Layout	34LYA063
Eff. date	02-10-2025
CD Diagram	CD0005
Poles	06
Leads	9#18
Proprietary	False
Created date	01-01-0001

High Voltage Full Load Amps	0.7 a
Insulation Class	B
Inverter Code	Not Inverter
KVA Code	K
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3411M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	11.35 IN
Power Factor	51
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.35
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1140 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2

None

Nameplate

NP1256L											
CAT.NO.	VM3531										
SPEC.	34A63-5882										
HP	.25										
VOLTS	230/460										
AMP	1.4/.7										
RPM	1140										
FRAME	56C		HZ	60			PH	3			
SER.F.	1.35	CODE	K	DES	B		CLASS	B			
NEMA-NOM-EFF	68	PF	51								
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	TEFC	SN									
	SFA 1.5/.75										

AC Induction Motor Performance Data

Record # 6830

Typical performance - not guaranteed values

Winding: 34WG5882-R001			Type: 3411M		Enclosure: TEFC		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		.25		Full Load Torque		1.15 LB-FT	
Volts		230/460		Start Configuration		direct on line	
Full Load Amps		1.4/.7		Breakdown Torque		3.8 LB-FT	
R.P.M.		1140		Pull-up Torque		2.9 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		3 LB-FT	
NEMA Design Code		B	KVA Code	K	Starting Current		2.5 A
Service Factor (S.F.)		1.35		No-load Current		0.57 A	
NEMA Nom. Eff.		68	Power Factor	51	Line-line Res. @ 25°C		80.7 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		41°C	
S.F. Amps		1.5/.75		Temp. Rise @ S.F. Load		53°C	

Load Characteristics 460 V, 60 Hz, 0.25 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	24	34	43	51	58	61	61
Efficiency	44	57	64	67.4	68	67.7	68.2
Speed	1184	1171	1157	1139	1122	1109	1115
Line amperes	0.57	0.6	0.63	0.68	0.73	0.78	0.75

ABB Motors and Mechanical Inc.

WINDING # 34WG5882

Typical performance - not guaranteed values.

0.25 HP 3 PH 60 HZ 1140 RPM 460 V 3411M

TORQUES (LB-FT) : PO=3.8 PU=2.9 LR=3 LRA=2.5





