

**BALDOR • RELIANCE**

---

# Customer information packet

## VM3541-57

AC MTR .56KW 2P, 3PH, 240/415V, 50HZ, 56C

Class - None

Division - Not Applicable

## Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.750 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	3000 RPM @ 50 HZ
Voltage @ Frequency	230.0 V @ 50 HZ 400.0 V @ 50 HZ
Agency Approvals	CE CSA IE2 UR WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.400 A @ 230.0 V 1.400 A @ 400.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard

## Part detail

Revision	V
Type	AC
Mech. spec.	34A063
Base	
Status	PRD/A
Elec. spec.	34WGY004
Layout	34LYA063
Eff. date	02-10-2025
CD Diagram	CD0022
Poles	02
Leads	6#18
Proprietary	False
Created date	09-07-2011

Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	1.4 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	M
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3420M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.35 IN
Power Factor	75
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	2850 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None

<b>Vibration Sensor Indicator</b>	<b>No Vibration Sensor</b>
<b>Winding Thermal 1</b>	<b>None</b>
<b>Winding Thermal 2</b>	<b>None</b>

**Nameplate**

**NP2717L**

<b>CAT NO</b>	VM3541-57						
<b>SPEC.</b>	34A063Y004G1						
<b>HP</b>	.75/KW	.56	<b>PH</b>	3			
<b>VOLTS</b>	230/400						
<b>AMP</b>	2.4/1.4						
<b>RPM</b>	2850 1/MIN						
<b>FRAME</b>	56C	<b>HZ</b>	50	<b>I.P.</b>	44		
<b>SER.F.</b>	1.25	<b>CODE</b>	M	<b>DES</b>	B	<b>CL</b>	F
<b>NEMA-NOM-EFF</b>	75.5						<b>% (100%)</b>
<b>PF</b>	75						
<b>RATING</b>	40C AMB-CONT				<b>CC</b>		
<b>DE BRG</b>	6203	<b>ODE</b>	6203				
<b>ENCL</b>	TEFC	<b>SN</b>					
<b>BLANK</b>	SFA 2.8/1.6						
	KG11 IC411						
	IE2-50HZ-74.5(75%)69.5(50%)						

**AC Induction Motor Performance Data**

Record # 35179

Typical performance - not guaranteed values

Winding: 34WGY004-R003		Type: 3420M	Enclosure: TEFC	
<b>Nameplate Data</b>			<b>400 V, 50 Hz: High Voltage Connection</b>	
Rated Output (HP)	.75	Full Load Torque	1.35 LB-FT	
Volts	230/400	Start Configuration	direct on line	
Full Load Amps	2.4/1.4	Breakdown Torque	6.47 LB-FT	
R.P.M.	2850	Pull-up Torque	4.81 LB-FT	
Hz	50 Phase	3	Locked-rotor Torque	5.24 LB-FT
NEMA Design Code	B KVA Code	M	Starting Current	10.3 A
Service Factor (S.F.)	1.25	No-load Current	0.849 A	
NEMA Nom. Eff.	75.5 Power Factor	69	Line-line Res. @ 25°C	16.8 Ω
Rating - Duty	40C AMB-CONT	Temp. Rise @ Rated Load		
S.F. Amps	2.8/1.6	Temp. Rise @ S.F. Load		
		Locked-rotor Power Factor	77	
		Rotor inertia	0.0186 LB-FT <sup>2</sup>	

**Load Characteristics 400 V, 50 Hz, 0.75 HP**

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	43	56	68	75	80	85	80
Efficiency	52.9	69.5	74.5	77.2	77.4	77.2	77.4
Speed	2967	2945	2920	2897	2872	2844	2872
Line amperes	0.917	1.05	1.21	1.38	1.58	1.77	1.58


ABB Motors and Mechanical Inc.

WINDING # 34WGY004

0.75 HP 3 PH 50 HZ 2850 RPM 400 V 3420M



Typical performance - not guaranteed values.

TORQUES (LB-FT): PO=6.47 PU=4.81 LR=5.24 LRA=10.3



6/9/2025 ACPERF, record # 35179

34LYA063



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CLEAN UP DIMENSIONING

REV: P	VERSION: 05	REVISED: 08:51:08 10/31/2024	TDR: 000001243684
--------	-------------	------------------------------	-------------------

34LYA063

MODEL NO. 34LYA063

BY: ENJEFD0


REF: -

**BALDOR - RELIANCE®**


STD VERT 34M NEMA 56C TEFC

34LYA063

CD0022




LOW VOLTAGE  
(1D)



LINE

HIGH VOLTAGE  
(1Y)



LINE

NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: F	BY: JLP	REVISED: 01/21/99 3:54	TDR: 0171435
CD0022		FILE: AAA00005144	MDL: -
		MTL: -	

**BALDOR ELECTRIC Co.**

3PH, DV, 6 LEADS, DELTA/WYE CONNECTION

CD0022