



Customer information packet

VNM3538

.5HP, 1720RPM, 3PH, 60HZ, 56C, 3416M, TENV, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TENV
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ 230.0 V @ 60 HZ 208.0 V @ 60 HZ
Agency Approvals	CSA UR
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	1.700 A @ 208.0 V 1.600 A @ 230.0 V .800 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	75.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater

Part detail

Revision	B
Type	AC
Mech. spec.	34K013
Base	
Status	PRD/A
Elec. spec.	34WGR706
Layout	34LYK013
Eff. date	10-25-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	01-29-2021

High Voltage Full Load Amps	0.8 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3416M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	10.25 IN
Power Factor	75
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.00
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1720 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.	VNM3538										
SPEC.	34K013R706										
HP	.5										
VOLTS	208-230/460										
AMP	1.7-1.6/.8										
RPM	1720										
FRAME	56C		HZ	60		PH	3				
SER.F.	1.00	CODE	J	DES	B	CLASS	F				
NEMA-NOM-EFF	75.5	PF	75								
RATING	40C AMB-CONT										
CC											
DE	6203		ODE	6203							
ENCL	TENV	SN									

AC Induction Motor Performance Data

Record # 86433

Typical performance - not guaranteed values

Winding: 34WGR706-R004			Type: 3416M		Enclosure: TENV		
Nameplate Data				460 V, 60 Hz: High Voltage Connection			
Rated Output (HP)		0.5		Full Load Torque		1.53 LB-FT	
Volts		208-230/460		Start Configuration		direct on line	
Full Load Amps		1.7-1.6/0.8		Breakdown Torque		5.15 LB-FT	
R.P.M.		1720		Pull-up Torque		2.87 LB-FT	
Hz	60	Phase	3	Locked-rotor Torque		3.94 LB-FT	
NEMA Design Code		B		KVA Code	J	Starting Current	5 A
Service Factor (S.F.)		1		No-load Current		0.577 A	
NEMA Nom. Eff.		75.5	Power Factor	75	Line-line Res. @ 25°C		48.9 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		78°C	
				Locked-rotor Power Factor		70.8	
				Rotor inertia		0.0381 lb-ft²	

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150
Power Factor	34	53	66	75	81	84
Efficiency	58.6	70.6	74.6	75.5	74.8	72.9
Speed	1779	1761	1741	1718	1692	1662
Line amperes	0.583	0.631	0.712	0.824	0.962	1.14

ABB Motors and Mechanical Inc.

WINDING # 34WGR706

Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 1720 RPM 460 V 3416M

TORQUES (LB-FT): PO=5.15 PU=2.87 LR=3.94 LRA=5





