



Customer information packet

VUHM3538

.5/.37KWHP, 1775RPM, 3PH, 60HZ, 56C, 3514M, TE

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ 460.0 V @ 60 HZ
Agency Approvals	C UR US CE CURUS UKCA WEEE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	2.020 A @ 230.0 V 1.010 A @ 460.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None

Part detail

Revision	C
Type	AC
Mech. spec.	35X042
Base	
Status	PRD/A
Elec. spec.	35WGG069
Layout	35LYX042
Eff. date	04-16-2024
CD Diagram	CD0005
Poles	04
Leads	9#18
Proprietary	False
Created date	09-15-2023

Heater Indicator	No Heater
High Voltage Full Load Amps	1.0 a
Insulation Class	F
Inverter Code	Not Inverter
KVA Code	N
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	9 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3514M
Mounting Arrangement	F3
Number of Poles	4
Overall Length	13.23 IN
Power Factor	63
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1775 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L												
CAT.NO.	VUHM3538											
SPEC.	35X042G069G2											
HP	.5/.37KW											
VOLTS	230/460											
AMP	2.02/1.01											
R.P.M. (1/MIN)	1775											
FRAME	56C		HZ		60			PH		3		
SER.F.	1.15	CODE		N	DES	B	CL	F				
NEMA-NOM-EFF	81.5	PF		63								
RATING	40C AMB-S1 CONT											
CC	010A		IP44 IC411 14KG									
DE	6205		ODE		6203							
ENCL	TEFC	SN										
	IE2-79.0(75%)74.0(50%)											

AC Induction Motor Performance Data

Record # 101694

Typical performance - not guaranteed values

Winding: 35WGG069-R086			Type: 3514M		Enclosure: TEFC				
Nameplate Data				460 V, 60 Hz: High Voltage Connection					
Rated Output (HP)		.5		Full Load Torque		1.48 LB-FT			
Volts		230/460		Start Configuration		direct on line			
Full Load Amps		2.02/1.01		Breakdown Torque		8 LB-FT			
R.P.M.		1775		Pull-up Torque		4.4 LB-FT			
Hz		60 Phase		3		Locked-rotor Torque	5.1 LB-FT		
NEMA Design Code		B		KVA Code		N	Starting Current	8.4 A	
Service Factor (S.F.)		1.15		No-load Current		0.85 A			
NEMA Nom. Eff.		81.5		Power Factor		63		Line-line Res. @ 25°C	30.3 Ω
Rating - Duty		40C AMB-CONT		Temp. Rise @ Rated Load		23°C			
S.F. Amps				Temp. Rise @ S.F. Load		25°C			
				Locked-rotor Power Factor		66.8			
				Rotor inertia		0.101 lb-ft²			

Load Characteristics 460 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	24	37	48	58	65	71	62
Efficiency	58.9	72.5	78.4	80.5	81.6	81.5	81.2
Speed	1793	1788	1782	1776	1771	1763	1773
Line amperes	0.85	0.89	0.94	1.01	1.11	1.21	1.07

ABB Motors and Mechanical Inc.

WINDING # 35WGG069

Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 1775 RPM 460 V 3514M

TORQUES (LB-FT) : PO=8 PU=4.4 LR=5.1 LRA=8.4





