

Ballymore's mini scissor lift work platforms are uniquely engineered for easy use and maneuverability in narrow aisles and tight access areas. It's the perfect lift for one man maintenance jobs in high, hard to reach areas, providing safe vertical access to working heights up to 19'



MINI SCISSOR LIFT

PUSHABLE MODELS

Mini Scissor Lifts are manufactured from durable, heavy duty steel. Safety features include top and mid rail guards with a hinged gate for easy and safe access. Platform includes toe guards to prevent slips and falls.

NO OUTRIGGERS REQUIRED!

*Floor Locks secure lift safely to the floor.
Small footprint enables easy access to limited access areas*

- **500 LB. CAPACITY**
- Manually Propelled
- Working heights up to 19'
- Maximum raised platform height of 9' 10" to 12' 9"
- 28" x 50" Platforms
- Easy to roll on 6" casters
- 12 Volt DC Powered
- Power Unit stored in a lockable slide out drawer
- Battery charge indicator is included
- Emergency stop button
- Emergency lowering system
- Forklift Pockets
- Complies with applicable OSHA & ANSI standards*
- Designed for indoor use

MODEL #	WORKING HEIGHT	PLATFORM MAX.	PLATFORM MIN.	FOOTPRINT W"x L"	OVERALL HEIGHT (LOWERED)	WEIGHT LBS
MSL-10	16'	9' 10"	26"	30" x 57"	77"	1,200
MSL-12	19'	12' 9"	26"	30" x 57"	77"	1,260

THE MINI MERCHANDISE LIFT

**Footprint only 26"W X 53"L
Great for tight aisle ways!**

Features

- Shelf Lip to prevent packages from falling off the front of the lift
- Safety Control Panel- 3 button plus Kill Switch
- Manual Lowering Valve
- Limit Switch included. This prevents the lift from ascending without the casters being locked to the floor.
- "Push" handles added to the front and back of the lift for easy maneuverability
- Safety shield to prevent access to internals
- Enlarged Standing Platform for added safety and comfort
- Saloon Door Gate
- Bubble Level
- Meets ANSI Standards



MODEL #BMML-9

THE MINI MERCHANDISE LIFT (BMML-9)

- **500LB. CAPACITY**
- Base = 26" Wide X 53" Long - (60" overall length including push rails)
- Merchandise Shelf = 25" Wide X 17" Long
- Overall Height = 55"
- Fully Lowered Standing Platform = 13"
- Standing Platform = 23^{1/2}" Wide X 26" deep
- Wheels - 4- 6" diameter
 - 2 - 2" Wide Locking Swivels
 - 2 - 2" Wide Rigid Wheels
- Shelf Height Maximum = 110"
- Standing Platform Maximum Height = 70"
- Color Yellow
- Power - 12V
- Weight = 840 lbs Approximate
- Shelf Capacity - 150lbs (tested)
- Complies with applicable OSHA & ANSI standards
- Designed for indoor use

