


Dry Poppet Couplings

FEATURES

- Lightweight.
- Minimal fluid spillage.
- Easy to use.
- Economical.
- Reduces risk of exposure.
- Wide range of chemical resistance.
- Maximum operating pressure 70 P.S.I. @ 70°F.
- Maximum operating temperature 150°F.
- 30 GPM maximum flow.
- Precision molded in polypropylene.
- 1" Female NPT threads.

APPLICATIONS

- Agriculture
- Industrial
- Pharmaceutical
- Chemical processing



Male Adapter & Female Coupler shown coupled together but sold separately.

DRY POPPET COUPLINGS			
PART NO	DESCRIPTION	QTY	PRICE
DPCF100	Female Dry Poppet Coupler, 1" Female NPT Threads w/ FKM (viton type) Seals	1	\$144.40
DPCM100	Male Dry Poppet Adapter, 1" Female NPT Threads w/ FKM (viton type) Seals	1	\$131.33
DPCMT100	Male Dry Poppet Adapter, w/2" Male Threaded Body, 1" Female NPT Threads w/ FKM (viton type) Seals	1	\$131.33



Male Adapter Dry Poppet DPCM100

2" Male NPT Thread



Male Adapter Dry Poppet DPCMT100



Female Coupling Dry Poppet DPCF100