

SmartDrop X

- Full-spectrum absorbance scans from 200 to 800nm
- Quickly calculates and displays 260/280 and 260/230 ratios
- Long-life Xenon lamp and linear array CCD detector
- Auto-ranging path lengths of 0.2mm and 1.0mm
- Detect up to 4,500 ng/μl of dsDNA without dilution



A full spectrum UV-Vis spectrophotometer, *SmartDrop X* requires 0.5 to 2.0μl of sample. In addition to nucleic acid and protein calculations, the software has preset programs for BCA, Bradford and Lowry assays. A full spectrum analysis can be performed in about 6 seconds, aiding in the identification of unknowns. Up to 5 specific points on the spectrum can be selected for colorimetric readings output.


The long life Xenon lamp source requires no warm up and is paired with a highly sensitive CCD detector. To provide the most accurate results, the *SmartDrop X* utilizes 2 path lengths.



Cuvette port for OD600 and Fluorometer port

SmartDrop XF - Spectrophotometer + Fluorometer

- Full-spectrum absorbance scanning and calculations of 260/280 and 260/230 ratios
- Long-life Xenon lamp with linear array CCD detector
- Auto-ranging path lengths of 0.05mm, 0.2mm and 1.0mm
- Detect up to 15,000ng/μl of dsDNA without dilution
- Integrated fluorometer for sensitive quantitation of low concentration nucleic acids



This top of the line spectrophotometer can perform not only UV-Vis readings in the range of 200-800nm but also fluorescence readings. Like the *SmartDrop X*, the *SmartDrop XF* features predefined programs for nucleic acids, proteins, and various colorimetric assays. The patented, motorized system gently stretches the sample column and allows for three different path lengths, providing accurate readings of samples from 0.5 to 2.0μl without dilution.

The integrated fluorometer yields more accurate, sensitive and selective quantitation of nucleic acids. The blue light channel (460nm) is useful for detection of dyes such as PicoGreen and RiboGreen as well as GFP and fluorescein. UV, green and red channel models are available upon request.

Specifications

Model	SmartDrop L (NS1000)	SmartDrop X (NS1010)	SmartDrop XF (NS1020)
Display	7-inch touch screen	7-inch touch screen	7-inch touch screen
Minimum sample size	1.0µl - 2.0µl	0.5µl - 2.0µl	0.5µl - 2.0µl
Path length	0.5mm	0.2mm, 1.0mm	0.05mm, 0.2mm, 1.0mm
Light source	UV LED	Xenon Flash Lamp	Xenon Flash Lamp
Detector	UV Silicon Photocell	2048 Element Linear Silicon CCD Array	2048 Element Linear Silicon CCD Array
Wavelength	260, 280, & 600nm	200 - 800nm (1nm steps)	200 - 800nm (1nm steps)
Absorbance range	0.2 - 50 A (10mm equivalent)	0.04 - 90 A (10mm equivalent)	0.04 - 300 A (10mm equivalent)
Absorbance precision	0.005 A	0.003 A	0.003 A
Lower limit of detection	dsDNA: 10ng/µl	dsDNA: 2ng/µl; BSA: 0.1mg/ml	dsDNA: 2ng/µl ; BSA: 0.1mg/ml
Upper limit of detection	dsDNA: 2,500ng/µl	dsDNA: 4,500ng/µl; BSA: 135mg/ml	dsDNA: 15,000ng/µl; BSA: 360mg/ml
Detection time	< 6 seconds	< 5 seconds	< 6 seconds
Communication ports	USB for data export	USB for data export	USB for data export
Voltage input	DC 24V, 2A	DC 24V, 2A	DC 24V, 2A
Power	25W	25W	25W
Dimensions (WxDxH)	20.8 x 8.0 x 18.6 cm / 8.2 x 11.0 x 7.3 in.	20.8 x 28.0 x 18.6 cm / 8.2 x 11.0 x 7.3 in.	20.8 x 28.0 x 18.6 cm / 8.2 x 11.0 x 7.3 in.
Weight	3.6 kg / 7.9 lbs	2.8 kg / 6.2 lbs	3.6 kg / 7.9 lbs
Cuvette OD600 detection			
Absorbance range	0.0 - 4.0 A	0.0 - 4.0 A	0.0 - 4.0 A
Absorbance stability	[0,3] ≤ 0.5%, [3,4] ≤ 2%	[0,3] ≤ 0.5%, [3,4] ≤ 2%	[0,3] ≤ 0.5%, [3,4] ≤ 2%
Absorbance repeatability	[0,3] ≤ 0.5%, [3,4] ≤ 2%	[0,3] ≤ 0.5%, [3,4] ≤ 2%	[0,3] ≤ 0.5%, [3,4] ≤ 2%
Absorbance precision	[0,2] ≤ 0.005 A, [2,3] ≤ 1%, [3,4] ≤ 2%	[0,2] ≤ 0.005 A, [2,3] ≤ 1%, [3,4] ≤ 2%	[0,2] ≤ 0.005 A, [2,3] ≤ 1%, [3,4] ≤ 2%
Fluorescence detection			
Excitation/Emission**	N/A	N/A	460 ± 20nm / 525-570nm
Sensitivity	N/A	N/A	dsDNA: 0.5pg/µl
Linearity	N/A	N/A	R ² ≥ 0.995
Repeatability	N/A	N/A	≤ 1.5%
Stability	N/A	N/A	≤ 1.5%

Ordering Information

Cat No.	Description
NS1000*	SmartDrop™ L Nano Spectrophotometer
NS1010*	SmartDrop™ X Nano Spectrophotometer
NS1020*	SmartDrop™ XF Nano Spectrophotometer
NS1020-HS-100	High Sensitivity DNA Quantitation Kit, 100 assays
NS1020-BR-100	Broad Range dsDNA Quantitation Kit, 100 assays
NS1000-C	Additional Standard-Size Cuvettes, pack of 2
NS1020-T	0.5mL Fluorescence Detection Tubes, pack of 250
NS1000-PA	Extra Paper Roll for SmartDrop internal printer, pack of 3

* Use part number "-E" to indicate 240V input and specify required plug type.

** Standard model includes blue channel. UV, green, & red channels available.

