


Versions / options for light-duty castors

1

Synthetic expander fitting for round tubes *

Product code suffix for LRA series	Product code suffix for LKRA series	Internal tube dimension (P) [mm]	Available for all swivel castors in the LRA/LKRA series with bolt hole \varnothing 11 mm. Swivel castor and expander secured to prevent loosening with positive locking. Maximum fitting length is 65 mm. Increases total height of swivel castors by 3 mm.
-ER02	-ER12	\varnothing 20–25	Detailed description: page 105
-ER03	-ER13	\varnothing 25–30	
-ER04	-ER14	\varnothing 30–35	
-ER05	-ER15	\varnothing 35–40	


* Corrosion-resistant versions page 398



Synthetic expander fitting for square tubes *


Product code suffix for LRA series	Product code suffix for LKRA series	Internal tube dimension (P) [mm]	Available for all swivel castors in the LRA/LKRA series with bolt hole \varnothing 11 mm. Swivel castor and expander secured to prevent loosening with positive locking. Maximum fitting length is 65 mm. Increases total height of swivel castors by 3 mm.
-EV02	-EV12	\square 18–21	Detailed description: page 105
-EV03	-EV13	\square 21–25	
-EV04	-EV14	\square 25–29	
-EV05	-EV15	\square 29–32	
-EV07	-EV17	\square 32–38.5	
	-EV18	\square 35.5–41	

* Corrosion-resistant versions page 398



Metal expander fitting for round and square tubes


Product code suffix for LRA series	Product code suffix for LKRA series	Internal tube dimension round tube (P) [mm]	Internal tube dimension square tube (P) [mm]	Available for all swivel castors in the LRA/LKRA series with bolt hole \varnothing 11 mm. Swivel castor and expander secured against rotation by positive locking. Maximum fitting length is 65 mm. Increases total height of swivel castors by 3 mm.
-E01	-E11	\varnothing 17–19	\square 17–19	Detailed description: page 105
-E02	-E12	\varnothing 20–25	\square 18–21	
-E03	-E13	\varnothing 25–30	\square 21–25	
-E04	-E14	\varnothing 30–35	\square 25–29	
-E05	-E15	\varnothing 35–40	\square 29–32	
-E07	-E17	\varnothing 39–45	\square 32–38.5	



Synthetic castor socket for round tube

Product code	Internal tube dimension round tube (P) [mm]	Flange dimension \varnothing (d) x height (B) [mm]	Fitting length castor sockets (Q) [mm]	Available for all swivel castors with plug-in pin \varnothing (d) 11 x 30.5 mm in the LRA series. Detailed description: page 105
RHR 20-18/11A	\varnothing 18.0	\varnothing 20.0 x 5.0	42	
RHR 22-19/11A	\varnothing 19.0	\varnothing 22.0 x 5.0	42	

Other dimensions are available upon request



Buffers for round and square tubes

Product code	Wheel \varnothing (D) [mm]	Wheel width (T1) [mm]	Hole (d) [mm]	Buffers reduce the risk of damage to walls and vehicles in the event of a collision. Buffers for round and square tubes are fixed or connected to tubular frames in the external areas of vehicles. AG series: Made from soft synthetic polyethylene, hardness 48 Shore D, colour silver grey RAL 7001, non-marking. ARG series: Made from solid rubber, hardness 75 Shore A, colour grey, non-marking. Detailed description: page 116
Synthetic buffers (polyethylene)				
AG 100/R25	100	17.5	\varnothing 25	
AG 100/V25	100	17.5	\square 25 x 25	
AG 125/R25	125	17.5	\varnothing 25	
AG 125/V25	125	17.5	\square 25 x 25	
Solid rubber buffers				
ARG 75/R10	75	23	\varnothing 10	
ARG 100/R26	100	23	\varnothing 26	
ARG 100/R32	100	23	\varnothing 32	
ARG 125/R26	125	23	\varnothing 26	
ARG 125/R32	125	23	\varnothing 32	

Other dimensions and special colours available upon request

