

Series: LMDA-TPA


**Light duty twin wheel castors with bolt hole fitting, wheels with thermoplastic rubber tread**

80 - 100 kg

RoHS



1



**Brackets:** LMDA series - Made of pressed steel, with double ball bearing in the swivel head, ball protection by the special top plate and ball disc design, dynamically pressed swivel head.  
 Bolted wheel axle.  
 Zinc-plated, blue-passivated, Cr6-free.  
 Bracket overview: Page 62  
 Wheel and swivel head 'stop-fix' brake: Page 80

**Wheels:** TPA series - Tread: Made of high-quality thermoplastic rubber-elastomer (TPE), containing traces of oil, 85° shore A, grey, non-marking.  
 Wheel centre: Made of high-quality, impact-resistant polypropylene, silver grey (black for electrically conductive '-ELS' version).  
 Bearing types: Plain bore or a centrally encapsulated ball bearing (C). Ball bearing (C) with synthetic thread guard as standard.  
 Detailed description: Page 88 and 42

Swivel castors	Swivel castors with 'stop-fix' brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate Ø [mm]	Bolt hole Ø [mm]	Offset [mm]
LMDA-TPA 50G	LMDA-TPA 50G-FI	50	2 x 19	80	Plain bore	71	41	10.2	31
LMDA-TPA 50K-FK	LMDA-TPA 50K-FI-FK	50	2 x 19	80	Ball bearing (C)	71	41	10.2	31
LMDA-TPA 75G	LMDA-TPA 75G-FI	75	2 x 25	100	Plain bore	98	55	10.2	34
LMDA-TPA 75K-FK	LMDA-TPA 75K-FI-FK	75	2 x 25	100	Ball bearing (C)	98	55	10.2	34

**Options**



	Image plain bore version	Electrically conductive version, non-marking grey
Technical description page		36, 38
Product code suffix		-ELS
Available for		all sizes