

LO-SE, BO-SE series

**Welded steel heavy-duty castors,
wheel with "Blickle EasyRoll" elastic solid rubber tyre**

320–850 kg

Bracket: LO/BO series

- solid welded steel construction, zinc-plated, blue-passivated, Cr6-free

Swivel bracket:


- double ball bearing in the swivel head
- **four specially-shaped, hardened bearing seats** for additional strength
- bolted and secured welded central kingpin, extremely strong
- swivel head seal with labyrinth design
- grease nipple

Wheel: SE series

- tyre: high-quality elastic solid rubber "Blickle EasyRoll" in smooth rolling quality, hardness 65 Shore A, colour black
- wheel centre: thick-walled pressed steel, with tubular steel hub, lacquered, colour black. wheel Ø 125 mm made from high-quality nylon 6, impact resistant, colour black

Additional details:

- bracket series: page 93
- brakes: page 112–113
- wheel series: page 228
- bearing types: page 84–85



Swivel castors	Fixed castors	Swivel castor with "stop-top" brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate size [mm]	Bolt hole spacing [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]
LO-SE 125K	BO-SE 125K	LO-SE 125K-ST	125	53	320	ball bearing	170	140 x 110	105 x 75–80	11	50
LO-SE 160K	BO-SE 160K	LO-SE 160K-ST	160	50	450	ball bearing	205	140 x 110	105 x 75–80	11	55
LO-SE 200K	BO-SE 200K	LO-SE 200K-ST	200	50	600	ball bearing	245	140 x 110	105 x 75–80	11	60
LO-SE 202K	BO-SE 202K	LO-SE 202K-ST	200	80	850	ball bearing	245	140 x 110	105 x 75–80	11	65
LO-SE 250K	BO-SE 250K	LO-SE 250K-ST	250	60	850	ball bearing	295	140 x 110	105 x 75–80	11	70

Versions / options



	with non-marking grey tyre	with directional lock 4 x 90°	with steel foot guard	truck lock
Technical description page	52	115	116	114
Product code suffix	-SG	-RI4	-FS	FF 125 / 160 / 200
Available for	wheel Ø 125–200 mm, others upon request	wheel Ø 125–200x50 mm	upon request	wheel Ø 125–200 mm