

L-G, B-G series

**Pressed steel castors, medium-duty version,
with top plate,
with cast iron wheel**



200–400 kg

Bracket: L/B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Swivel bracket:


- double ball bearing in the swivel head
- strong central kingpin (from wheel Ø 150 mm)
- swivel head seal
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: G series

- rugged grey cast iron, hardness 180–220 HB, grease nipple, lacquered, colour silver

Additional details:

- bracket series: page 91
- brakes: page 112–113
- wheel series: page 376
- bearing types: page 84–85



Swivel castors	Fixed castors	Swivel castors with "stop-fix" brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate size [mm]	Bolt hole spacing [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]
L-G 80G	B-G 80G	L-G 80G-FI	80	25	200	plain bore	102	100 x 85	80 x 60	9	38
L-G 100G	B-G 100G	L-G 100G-FI	100	35	200	plain bore	125	100 x 85	80 x 60	9	36
L-G 125G	B-G 125G	L-G 125G-FI	125	35	200	plain bore	150	100 x 85	80 x 60	9	38
L-G 150G	B-G 150G	L-G 150G-FI	150	50	400	plain bore	190	140 x 110	105 x 75–80	11	60
L-G 200G	B-G 200G	L-G 200G-FI	200	50	400	plain bore	235	140 x 110	105 x 75–80	11	65

7

Versions / options



	with "stop-top" brake	directional lock (separate) 1 x 360°	directional lock (separate) 1 x 360°	with steel foot guard	heat-resistant versions
Technical description page	112	115	115	116	59, 97–99
Product code suffix	-ST	RI-03.01	RI-05.03	-FS	
Available for	all	wheel Ø 100–125 mm*	wheel Ø 150–200 mm*	wheel Ø 100–200 mm upon request	see series LI-G (page 469)

* Only for swivel castors without brake or swivel castor with "stop-top" brake upon request