

Wraprot™ A6500 Wire ID Printer Applicator

Materials for Wraprot™ Wire ID Printers

The following catalog numbers beginning with "WRAP" are specially designed for use in the new Wraprot A6500 Printer and the legacy Wraprot Printer (#WRAPTOR-PTR).

B-427 Self-Laminating Wire Material

Color: White/Clear

Finish: Matte

Self-laminating vinyl features white printable area with a clear "tail" that wraps around marker. Tail serves as overlamine to protect the print. Superior resistance to abrasion, solvents, water, oil and dirt.

Performance Attributes:




Figure 14



Diagram	Catalog #	Material	Color	Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Write On Area F Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 14	WRAP-1-427	Vinyl	White	18-22g; 0.06" - 0.08" dia	0.500 (12.7)	0.750 (19.1)	0.875 (22.2)	0.790 (20.1)	0.375 (9.5)	1	6800	R4311
Fig. 14	WRAP-2-427	Vinyl	White	12-18g; 0.08" - 0.159" dia	1.000 (25.4)	1.000 (25.4)	1.125 (28.6)	1.290 (32.8)	0.375 (9.5)	1	5300	R4306
Fig. 14	WRAP-3-427	Vinyl	White	10-14g; 0.159" - 0.199" dia	1.000 (25.4)	1.250 (31.8)	1.375 (34.9)	1.290 (32.8)	0.500 (12.7)	1	4300	R4306
Fig. 14	WRAP-11-427	Vinyl	White	6-14g; 0.159" - 0.279" dia	0.500 (12.7)	1.500 (38.1)	1.625 (41.3)	0.790 (20.1)	0.500 (12.7)	1	3600	R4311
Fig. 14	WRAP-4-427	Vinyl	White	6-14g; 0.159" - 0.279" dia	1.000 (25.4)	1.500 (38.1)	1.625 (41.3)	1.290 (32.8)	0.500 (12.7)	1	3600	R4306
Fig. 14	WRAP-12-427	Vinyl	White	6-14g; 0.159" - 0.279" dia	2.000 (50.8)	1.500 (38.1)	1.625 (41.3)	2.290 (58.2)	0.500 (12.7)	1	3600	R4302
Fig. 14	WRAP-10-427	Vinyl	White	1/0-8g; 0.239" - 0.438" dia	1.000 (25.4)	2.250 (57.2)	2.375 (60.3)	1.290 (32.8)	0.750 (19.1)	1	2500	R4306
Fig. 14	WRAP-5-427	Vinyl	White	1/0-8g; 0.239" - 0.517" dia	1.000 (25.4)	2.500 (63.5)	2.625 (66.7)	1.790 (45.5)	0.750 (19.1)	1	2200	R4306
Fig. 14	WRAP-6-427	Vinyl	White	3/1-6g; 0.318" - 0.597" dia	2.000 (50.8)	3.000 (76.2)	3.125 (79.4)	2.290 (58.2)	1.000 (25.4)	1	1900	R4302

B-472 Polyimide Wirewrap Material

Color: White

Finish: Matte

Polyimide wire and cable material specifically designed to self-extinguish and prevent flames from propagating. This material is ideal for wire and cable identification in extreme environments, particularly in the aerospace, defense and mass transit industries.

Performance Attributes:




Figure 2



Diagram	Catalog #	Material	Color	Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 2	WRAP-1-472	Polyimide	White	10-14g; 0.159" - 0.199" dia	0.750 (19.1)	0.500 (12.7)	0.875 (22.2)	0.790 (20.1)	1	6800	R4311
Fig. 2	WRAP-6-472	Polyimide	White	3/0-8g; 0.212" - 0.597" dia	2.000 (50.8)	3.000 (76.2)	3.125 (79.4)	2.290 (58.2)	1	1900	R4302

B-499 Nylon Cloth Material

Color: White

Finish: Matte

Nylon cloth with permanent adhesive allows labeling in environments with heat, cold, oil and dirt. Ideal for wire and cable marking, electronic component marking, laboratory vial identification and general labeling.

Performance Attributes:




Figure 2



Diagram	Catalog #	Material	Color	Wire Gauge	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 2	WRAP-7-499	Nylon Cloth	White	10-22g; 0.06" - 0.199" dia	0.500 (12.7)	0.750 (19.1)	1	4500	R4311
Fig. 2	WRAP-13-499	Nylon Cloth	White	6-14g; 0.159" - 0.279" dia	1.000 (25.4)	1.000 (25.4)	1	4100	R4306
Fig. 2	WRAP-8-499	Nylon Cloth	White	2-14g; 0.159" - 0.438" dia	1.000 (25.4)	1.500 (38.1)	1	2800	R4306
Fig. 2	WRAP-9-499	Nylon Cloth	White	3/0-8g; 0.212" - 0.597" dia	2.000 (50.8)	2.000 (50.8)	1	2100	R4302