



SPECIFICATIONS - STOCK MINIMUM BORE GEARBELT® PULLEYS FOR "XL", 1/5" PITCH BELTS 1/4" AND 3/8" WIDE

TABLE No. 1.

PART NUMBER	DIAMETERS				NUMBER OF GROOVES	TYPE	BORE		DIMENSIONS				WT. Lbs.
	STEEL	PITCH	OUTSIDE	FLANGE			STOCK	MAX.	F	L	P	H	
10XLB037	10XLB037S	.637"	.617"	15/16"	10	2	3/16"	3/16"	9/16"	13/16"	1/4"	7/16"	.04
11XLB037	-	.700	.680	15/16"	11	2	3/16	3/16	9/16	13/16	1/4	1/2	.04
12XLB037	12XLB037S	.764	.744	1	12	2	3/16	1/4	9/16	13/16	1/4	1/2	.04
14XLB037	14XLB037S	.891	.871	1 1/8	14	2	1/4	1/4	9/16	13/16	1/4	9/16	.05
15XLB037	15XLB037S	.955	.935	1 3/16	15	2	1/4	5/16	9/16	13/16	1/4	5/8	.06
16XLB037	16XLB037S	1.019	.999	1 1/4	16	2	1/4	3/8	9/16	13/16	1/4	11/16	.06
18XLB037	18XLB037S	1.146	1.126	1 3/8	18	2	1/4	1/2	9/16	13/16	1/4	13/16	.08
20XLB037	20XLB037S	1.273	1.253	1 1/2	20	2	1/4	9/16	9/16	7/8	11/32	15/16	.10
21XLB037	21XLB037S	1.337	1.317	1 9/16	21	2	1/4	9/16	9/16	7/8	11/32	1	.11
22XLB037	22XLB037S	1.401	1.381	1 5/8	22	2	1/4	5/8	9/16	7/8	11/32	1	.12
24XLB037	24XLB037S	1.528	1.508	1 3/4	24	2	1/4	11/16	9/16	29/32	11/32	1 1/16	.13
28XLB037	28XLB037S	1.783	1.763	2	28	2	1/4	13/16	9/16	29/32	11/32	1 3/16	.13
30XLB037	30XLB037S	1.910	1.890	2 1/8	30	2	1/4	15/16	9/16	29/32	11/32	1 5/16	.13
32XLB037	32XLB037S	2.037	2.017	2 1/4	32	2A	5/16	1	9/16	29/32	7/16	1 7/16	.13
36XLB037	36XLB037S	2.292	2.272	-	36	2A	5/16	1	9/16	1	7/16	1 1/2	.19
40XLB037	40XLB037S	2.546	2.526	-	40	2A	5/16	1	9/16	1	7/16	1 1/2	.25
42XLB037	42XLB037S	2.674	2.654	-	42	2A	5/16	1	9/16	1	7/16	1 1/2	.31
44XLB037	44XLB037S	2.801	2.781	-	44	2A	5/16	1	9/16	1	7/16	1 1/2	.38
48XLB037	48XLB037S	3.056	3.036	-	48	2A	5/16	1	9/16	1	7/16	1 1/2	.38
60XLB037	60XLB037S	3.820	3.800	-	60	2A	3/8	1	9/16	1	7/16	1 1/2	.38
72XLB037	72XLB037S	4.584	4.564	-	72	2A	3/8	1	9/16	1	7/16	1 1/2	.44

Browning® Stock Minimum Bore Pulleys (shown above) for "XL" Gearbelt belts are made of aluminum. They are furnished without keyseats but with two Hollow Head Setscrews at 90 degrees, since most of these pulleys are used on applications which normally do not require a key. They can be bored to size and furnished with keyseat at a reasonable extra price. These pulleys are also stocked in steel or sintered steel material, available by adding 'S' to the end of the part number i.e., 16XLB037S.

STOCK "XL", 1/5" PITCH GEARBELT® BELTS

TABLE No. 2

PITCH LENGTH	No. TEETH	1/4" WIDE		3/8" WIDE	
		PART No.	WT. Lbs.	PART No.	WT. Lbs.
6.0"	30	60XL025	.006	60XL037	.009
7.0	35	70XL025	.007	70XL037	.011
8.0	40	80XL025	.008	80XL037	.012
9.0	45	90XL025	.009	90XL037	.014
10.0	50	100XL025	.011	100XL037	.015
11.0	55	110XL025	.012	110XL037	.017
12.0	60	120XL025	.013	120XL037	.018
13.0	65	130XL025	.014	130XL037	.020
14.0	70	140XL025	.015	140XL037	.021
15.0	75	150XL025	.016	150XL037	.023
16.0	80	160XL025	.017	160XL037	.024
17.0	85	170XL025	.018	170XL037	.026
18.0	90	180XL025	.019	180XL037	.027
19.0	95	190XL025	.020	190XL037	.029
20.0	100	200XL025	.021	200XL037	.030
21.0	105	210XL025	.022	210XL037	.032
22.0	110	220XL025	.023	220XL037	.033
23.0	115	230XL025	.024	230XL037	.035
24.0	120	240XL025	.025	240XL037	.036
25.0	125	250XL025	.026	250XL037	.038
26.0	130	260XL025	.027	260XL037	.039