



**T-Handle**

UDN5150 | UEN5200



**Ratchet Handle**  
UERN5200

### INSERTA CLAMPS

Place the Inserta Clamps into the 5/8" holes on the BuildPro® Tabletop, Riser Blocks, Economy Stops or Clamping Squares for fast, easy clamping. Clamp in the vertical or horizontal position at any height.

The Ratchet Handle Model is ideal for tight space clamping, and the ratchet mechanism ensures rapid, vibration and torsion resistant clamping.

Clip the optional Top V-Pads (pg. 29) onto the top spindle to clamp round or angled stock. Remove the clamp arm by depressing the spring stop, and slide the Sidekick attachment (pg. 29) onto the clamp bar, followed by the clamp arm, for two point horizontal and vertical clamping force.



Part No.	Clamping Capacity (in)	Throat Depth (in)	Clamping Pressure (lb)	Rail Size (in)	Weight (lb)
UDN5150	6-1/2	3-1/4	300	5/8 x 5/16	1.2
UEN5200	8-1/2	4	400	25/32 x 3/8	2.2
UERN5200	8-1/2	4	400	25/32 x 3/8	2.2

### SLIDING CHANNEL CLAMPS \*



The 360° Sliding Channel Clamp slides into the 1.7" spacing between plates which enables the clamp body to slide along the entire surface and swivel 360° for positioning at any point.



Part No.	Clamping Capacity (in)	Throat Depth (in)	Clamping Pressure (lb)	Rail Size (in)	Weight (lb)
T51405	8-1/2	4-3/4	500	7/8 x 7/16	3.5
T51510	12-1/2	4-3/4	600	1 x 15/32	4.8
T51615	20-1/2	5-1/2	700	1-3/16 x 9/16	8.2

\* Not applicable to BuildPro® MAX table.