




# 1PLD75010, UV Rated Black, 2-Side, 10-Port, 2 AWG-750 kcmil

By Burndy  
Catalog # [1PLD75010](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 10-Port Tap, #2 AWG-750 kcmil



## Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

## Specifications

|                                         |    |
|-----------------------------------------|----|
| Certification - UL Recognized           | No |
| Certification - cULus                   | No |
| Certification - ETL                     | No |
| Standards - RoHS Compliance             | CM |
| Status                                  |    |
| Certification - UL Listed Direct Burial | No |
| UL Listed                               | No |
| Certification - CSA Approved            | No |

## Conductor

|                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size       | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0 AWG</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 266 kcmil</li><li>• 300 kcmil</li><li>• 336 kcmil</li><li>• 350 kcmil</li><li>• 397 kcmil</li><li>• 400 kcmil</li><li>• 450 kcmil</li><li>• 477 kcmil</li><li>• 500 kcmil</li><li>• 550 kcmil</li><li>• 556 kcmil</li><li>• 600 kcmil</li><li>• 636 kcmil</li><li>• 650 kcmil</li><li>• 700 kcmil</li><li>• 715 kcmil</li><li>• 750 kcmil</li></ul> |
| Conductor - AL Str Size Range | 2 AWG - 750 kcmil                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |

|                                   |                                                                                                                                                                                                                                                                                                                                                     |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size       | <ul style="list-style-type: none"><li>• 2 AWG</li><li>• 1 AWG</li><li>• 1/0</li><li>• 2/0 AWG</li><li>• 3/0 AWG</li><li>• 4/0 AWG</li><li>• 250 kcmil</li><li>• 300 kcmil</li><li>• 350 kcmil</li><li>• 400 kcmil</li><li>• 450 kcmil</li><li>• 500 kcmil</li><li>• 550 kcmil</li><li>• 600 kcmil</li><li>• 700 kcmil</li><li>• 750 kcmil</li></ul> |
| Conductor Size                    | 2 AWG-750 KCMIL                                                                                                                                                                                                                                                                                                                                     |
| Conductor Type                    | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul>                                                                                                                                                                                                                                                             |
| Conductor - Copper Str Size Range | 2 AWG - 750 kcmil                                                                                                                                                                                                                                                                                                                                   |

## Configuration

|                                       |           |
|---------------------------------------|-----------|
| Physical Attribute - Number of Screws | 10        |
| Number Of Ports                       | 10        |
| Connector Type                        | Multi Tap |

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height mm           | 76.2 mm   |
| Dimension - Height inch         | 3.00 in   |
| Dimension - Height fraction     | 3 in      |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 164       |
| Width                           | 3.38 in   |
| Dimension - Screw Size inch     | 13/16     |
| Length                          | 13.87 in  |
| Dimension - Width mm            | 86 mm     |
| Dimension - Width inch          | 3.38 in   |

|                            |                           |
|----------------------------|---------------------------|
| Height                     | 3 in                      |
| Dimension - Length Overall | 13.87 in                  |
| inch                       |                           |
| Dimensions                 | 13.87 in x 3.38 in x 3 in |

General

|                                 |              |
|---------------------------------|--------------|
| Insulation Type                 | Plastisol    |
| Material - Hardware             | Aluminum     |
| Insulation                      | Y            |
| Physical Attribute - Screw Type | Allen        |
| Plated                          | N            |
| UPC                             | 781810287460 |
| Hex Key                         | 3/8          |
| Material                        | Aluminum     |

|                   |                |
|-------------------|----------------|
| Plating Type      | Unplated       |
| UPC 12 Digit      | 781810287460   |
| UPC 14 Digit GTIN | 00781810287460 |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 320 |
| Carton Quantity       | 10  |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)



A Hubbell brand