



1PLD7505HD, UV Rated Black, 2-Side, 5-Port, 2 AWG-750 kcmil

By Burndy
Catalog # [1PLD7505HD](#)

UV Rated Covering, Oxide inhibitor pre-installed 2-Sided, 5-Port Tap, Heavy Duty, #2 AWG-750 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	2 AWG-750 KCMIL
----------------	-----------------

Configuration

Number Of Ports	5
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Length	6.75 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	171.45 mm
Height	3 in
Width	4.83 in
Dimension - Length Overall	6.75 inch
Dimensions	6.75 in x 4.83 in x 3 in

Force Related

Installation Torque	500 in-lb
Recommended in-lb	

General

Trade Name	UNITAP™
UPC	621945480766
Hex Key	3/8 in
Material	Aluminum

Logistics

Pallet Quantity	162
Carton Quantity	6

Operational

Temperature Rating	-40°C to 135°C
--------------------	----------------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand