




1PLMD2506, UV Black, Mount, 2-Side, 6-Port, 10 AWG-250 kcmil

By Burndy
Catalog # 1PLMD2506



UV Rated Covering, Oxide inhibitor pre-installed, Mountable, 2-Sided, 6-Port Tap, #10 AWG-250 kcmil

Features

- UV Rated Covering over AL6061-T6 aluminum body saves time, lowering installation costs and eliminates taping
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces the number of connectors necessary to carry in inventory

- 3 AWG
- 2 AWG
- 1 AWG
- 1/0
- 2/0 AWG
- 3/0 AWG
- 4/0 AWG
- 250 kcmil

Specifications

Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10 AWG-250 KCMIL
Conductor - AL Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG • 3 AWG • 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - AL Str Size Range	10 AWG - 250 kcmil
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	10 AWG - 250 kcmil
Conductor - Copper Str Size	• 10 AWG • 9 AWG • 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG

Configuration

Physical Attribute - Number of Screws	8
Number Of Ports	6
Connector Type	Multi Tap

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - Height mm	56.6 mm
Length	7.4 in
Dimension - Height inch	2.13
Dimension - Height fraction	2-1/4 in
Dimension - Width mm	67 mm
Dimension - Width inch	2.64
Dimension - L Length Overall mm	188
Height	2.13 in
Width	2.64 in
Dimension - Length Overall inch	7.4
Dimensions	7.4 in x 2.64 in x 2.13 in


General

Plated	N
Insulation Type	Plastisol
Trade Name	UNITAP™
Material - Hardware	Aluminum
UPC	781810307595
Insulation	Y
Hex Key	5/16
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810307595
UPC 14 Digit GTIN	00781810307595

Logistics

Minimum Pack Quantity1

Operational



Temperature Rating

194° F

Product Assets

- Catalog [English]
- Catalog [English]