

BALDOR • RELIANCE

Customer information packet

VL3514-50

1.5/1.1KW, 1455RPM, 1PH, 50HZ, 56C, 3540LC, TE

Class - None

Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.

6/9/2025 3:55:19 AM

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	50.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.100 KW @ 50 HZ
Phase	1
Synchronous Speed @ Frequency	1500 RPM @ 50 HZ
Voltage @ Frequency	220.0 V @ 50 HZ
Agency Approvals	C UR US WEEE UKCA CURUS CE
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.200 A @ 220.0 V
Design Code	-
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	81.4 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.2 a

Part detail

Revision	F
Type	AC
Mech. spec.	35E022
Base	
Status	PRD/A
Elec. spec.	35WGG774
Layout	35LYE022
Eff. date	04-08-2025
CD Diagram	CD0017A02
Poles	04
Leads	4#18
Proprietary	False
Created date	10-10-2023

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Quantity/Wire Size	4 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3540LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	15.48 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	0.625 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1455 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1372L										
CAT.NO.	VL3514-50									
SPEC.	35E022G774									
HP	1.5/1.1KW									
VOLTS	220									
AMP	6.2									
R.P.M. (1/MIN)	1455									
FRAME	56C		HZ	50		PH	1			
SER.F.	1.15	CODE	J	DES	-	CL	F			
NEMA-NOM-EFF	81.4	PF	98							
RATING	40C AMB-S1 CONT									
CC			IP44 IC411 35KG							
DE	6205		ODE	6203						
ENCL	TEFC	SN								
	IE2-50HZ 81(75%),76(50%)									

AC Induction Motor Performance Data

Record # 101541

Typical performance - not guaranteed values

Winding: 35WGG774-R001		Type: 3540LC	Enclosure: TEFC	
Nameplate Data			220 V, 50 Hz: Single Voltage Motor	
Rated Output (KW)	1.1	Full Load Torque	5.317 LB-FT	
Volts	220	Start Configuration	direct on line	
Full Load Amps	6.2	Breakdown Torque	14.3 LB-FT	
R.P.M.	1455	Pull-up Torque	11.5 LB-FT	
Hz	50	Phase	1	Locked-rotor Torque
NEMA Design Code	-	KVA Code	J	Starting Current
Service Factor (S.F.)	1.15			No-load Current
NEMA Nom. Eff.	81.4	Power Factor	98	Line-line Res. @ 25°C
Rating - Duty			40C AMB-CONT	Temp. Rise @ Rated Load
S.F. Amps				Temp. Rise @ S.F. Load

Load Characteristics 220 V, 50 Hz, 1.1 KW

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	94	98	98	98	98	98	98
Efficiency	60.6	76.7	81.7	82.9	82.1	79.4	82.4
Speed	1488.5	1479	1468.7	1456.9	1442.7	1424.4	1448
Line amperes	2.21	3.36	4.67	6.13	7.74	9.61	7.1


ABB Motors and Mechanical Inc.

WINDING # 35WGG774


Typical performance - not guaranteed values.

1.1 KW 1 PH 50 HZ 1455 RPM 220 V 3540LC


TORQUES (LB-FT): PO=14.3 PU=11.5 LR=14.3 LRA=49.2



6/9/2025 ACPERF, record # 101541



CD0017A02



	LINE A	LINE B
STD	1,8	4,5
OPP	1,5	4,8

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0017A02

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			
REV. LTR: B	BY: JLP	REVISED: 04/09/99 11:30	TDR: 0178636
CD0017A02		FILE: AAA00007514	MDL: -
		MTL: -	

BALDOR ELECTRIC Co.

TYPE LC, SV, REV, 4 LEADS