



Customer information packet

VM3537-5

.5HP, 3450RPM, 3PH, 60HZ, 56C, 3410M, TEFC, F1

Class - None

Division - Not Applicable

Specifications

Enclosure	TEFC
Frame	56C
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	.500 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UR CSA
Ambient Temperature	40 °C
Auxillary Box	No Auxillary Box
Auxillary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	.800 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	68.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	0.8 a
Insulation Class	B
Inverter Code	Not Inverter

Part detail

Revision	Z
Type	AC
Mech. spec.	34A063
Base	
Status	PRD/A
Elec. spec.	34WG0487
Layout	34LYA063
Eff. date	02-10-2025
CD Diagram	CD0006
Poles	02
Leads	3#18
Proprietary	False
Created date	01-01-0001

KVA Code	J
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	3 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3410M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	11.35 IN
Power Factor	63
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.25
Shaft Diameter	0.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	3450 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L									
CAT.NO.	VM3537-5								
SPEC.	34A63-487								
HP	.5								
VOLTS	575								
AMP	.8								
RPM	3450								
FRAME	56C		HZ	60			PH	3	
SER.F.	1.25	CODE	J	DES	B	CLASS		B	
NEMA-NOM-EFF	68	PF	63						
RATING	40C AMB-CONT								
CC									
DE	6203		ODE	6203					
ENCL	TEFC	SN							
	SFA 1								

AC Induction Motor Performance Data

Record # 6584

Typical performance - not guaranteed values

Winding: 34WG0487-R001			Type: 3410M		Enclosure: TEFC			
Nameplate Data			575 V, 60 Hz: Single Voltage Motor					
Rated Output (HP)		.5	Full Load Torque		0.75 LB-FT			
Volts		575	Start Configuration		direct on line			
Full Load Amps		.8	Breakdown Torque		3.4 LB-FT			
R.P.M.		3450	Pull-up Torque		2.7 LB-FT			
Hz	60	Phase	3	Locked-rotor Torque		3 LB-FT		
NEMA Design Code		B	KVA Code	J	Starting Current		4.8 A	
Service Factor (S.F.)		1.25	No-load Current		0.72 A			
NEMA Nom. Eff.		68	Power Factor		63	Line-line Res. @ 25°C		56.4 Ω
Rating - Duty		40C	AMB-CONT		Temp. Rise @ Rated Load		58°C	
S.F. Amps		1	Temp. Rise @ S.F. Load		69°C			

Load Characteristics 575 V, 60 Hz, 0.5 HP

% of Rated Load	25	50	75	100	125	150	S.F.
Power Factor	33	44	56	64	70	77	70
Efficiency	41.4	56.3	64	67.2	68.4	68.5	68.4
Speed	3563	3535	3501	3466	3432	3381	3432
Line amperes	0.73	0.78	0.81	0.88	0.96	1.06	0.96


ABB Motors and Mechanical Inc.

WINDING # 34WG0487



Typical performance - not guaranteed values.

0.5 HP 3 PH 60 HZ 3450 RPM 575 V 3410M

TORQUES (LB-FT): PO=3.4 PU=2.7 LR=3 LRA=4.8



34LYA063



CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION

REV. DESC: CLEAN UP DIMENSIONING

REV: P

VERSION: 05

REVISED: 08:51:08 10/31/2024

TDR: 000001243684

34LYA063

MODEL NO. 34LYA063

REF: -

BY: ENJEFD0

BALDOR - RELIANCE®

STD VERT 34M NEMA 56C TEFC

34LYA063

CD0006

TYPICAL WYE-CONNECTED MOTOR

1-BLU

J-BRN

OPTIONAL THERMOSTATS

J-BRN

3-ORG

2-WHT

TYPICAL DELTA-CONNECTED MOTOR

1-BLU

J-BRN

2-WHT

OPTIONAL THERMOSTATS

J-BRN

3-ORG

1

2

3

LINE

NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.

2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.

3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.

4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.

5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE® 3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED SH 1 of 1
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10: 24: 49 02/19/2019	BY: ENBRIRO	
MTL: —			

CD0006

34WG0232: Electrical Design

Page 8 of 8