



AGSKIT2 Splice Kit, 8-2 AWG, Al/Cu Rated

By Burndy
Catalog # [AGSKIT2](#)

Splice Kit, 8-2 AWG, supplied with Heavy Wall Heat Shrink Sleeve, Al/Cu Rated



Features

- Dual Rated - Aluminum or Copper/Aluminum Combinations
- Installed with common installation tools
- Heavy wall heat shrink sleeve is lined with adhesive material providing a positive seal against moisture egress

- 6 AWG
- 5 AWG
- 4 AWG
- 3 AWG
- 2 AWG

Application

For All Aluminum or Copper/Aluminum Combinations

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	8-2 AWG
Conductor - Copper Solid Size	• 8 AWG • 7 AWG • 6 AWG • 5 AWG • 4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - AL Str Size	• 8 AWG • 6 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size Range	8 AWG-2 AWG
Conductor Type	• AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	• 8 AWG • 7 AWG

Configuration

Connector Type	Splice/Heat Shrink Kit
----------------	------------------------

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5 in
Hex Size	Slot

General

Physical Attribute - Screw Type	Slot
Plated	N
Material - Hardware	Aluminum
Sub Brand	SPLICE KIT
UPC	781810175293
Type	AGSKIT, Above Grade
Insulation	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810175293
UPC 14 Digit GTIN	00781810175293

Logistics

Pallet Quantity	960
Carton Quantity	10

Operational

Temperature Rating	194° F
--------------------	--------



A Hubbell brand