




ASA1000U, Terminal Stacking Adaptor, Al/Cu, 1000 kcmil

By Burndy
Catalog # [ASA1000U](#)



Used with standard NEMA 2- or 4-Hole terminals; to stack 4-Hole terminations, two stacking adapters are needed assembled side-by-side, AL/CU, 1000 kcmil

Features

- For use on terminals made from copper or aluminum
- May be used with standard NEMA two and four hole terminals
- TO stack four hole NEMA terminations use two stacking adapters assembled side-by-side
- Only three sizes necessary to accommodate terminals from 250 kcmil through 1000 kcmil

Application

For Aluminum And Copper Terminals

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - AL Str Size	• 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 266 kcmil • 300 kcmil • 336 kcmil • 350 kcmil • 397 kcmil • 400 kcmil • 450 kcmil • 477 kcmil • 500 kcmil • 550 kcmil • 556 kcmil • 600 kcmil • 636 kcmil • 650 kcmil
-------------------------	---

Conductor - AL Str Size Range	• 700 kcmil • 715 kcmil • 750 kcmil • 795 kcmil • 800 kcmil • 874 kcmil • 900 kcmil • 954 kcmil • 1000 kcmil
Conductor - Copper Str Size	1/0 AWG-1000 kcmil
Conductor Type	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil • AL C Str-Size • CU C Str-Size
Conductor - Copper Str Size Range	1/0 -1000 kcmil

Configuration

Physical Attribute - Number of Screws	2
Physical Attribute - Number of Holes	2

Current

Rating - Minimum Voltage	600
--------------------------	-----

Dimensions

Dimension - Pad Width inch	1.25 in
Package Height	0.000 in
Dimension - Height mm	31.8 mm


Dimension - Height inch	1.25 in
Dimension - Height fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	23 mm
Width	1.25 in
Length	3 in
Height	1.25 in
Dimension - Bolt Size inch	3.75 in
Dimension - Length Overall inch	0.91 in
Dimensions	3 in x 1.25 in x 1.25 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

Product Family	Power Connectors>Aluminum Compression Terminals & Splices>Stacking Adapters
Trade Name	HYSTACK™



Material - Hardware	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	Yes
Sub Brand	HYSTACK
Product Type	Mechanical
UPC	781810521045
Type	Stacking Adapters
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810521045
UPC 14 Digit GTIN	00781810521045

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	10

Operational

Temperature Rating	194° F
--------------------	--------

Product Assets

[Catalog \[English\]](#)