

AT22A19A30, Angled V Substation Connector

By Burndy
Catalog # [AT22A19A30](#)



Angled V Substation Connectors

Features

- Aluminum alloy T-Connector for tubing run to tubing (2) taps forming a 30 degree A Frame
- Captured hex head bolt permit one-wrench installation

Application

Substation

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	EX
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Tube Std Run Range	4 IPS
Conductor - AL Tube Std Run	4 IPS
Conductor - AL Tube Std Tap Range	2 1/2 IPS
Conductor - AL Tube Std Tap	2 1/2 IPS

Configuration

Physical Attribute - Pad Orientation	30 Degree
Physical Attribute - Number of Tap Conductors	2
Physical Attribute - Number of Run Conductors	1
Connector Type	A-Frame

Dimensions

Dimension - Height mm	285.2 mm
Length	11.87 in
Dimension - Height inch	11.23 in
Dimension - L Length Overall mm	301 mm
Dimension - B Length inch	6.00 in
Height	11.23 in
Width	4.5 in
Dimension - Length BB inch	4.50 in
Dimension - Length Overall inch	11.87 in
Connector Angle	30 Degree
Dimensions	11.87 in x 4.5 in x 11.23 in

Force Related

Installation Torque	480 lb-in
Recommended Tap in-lb	
Installation Torque	480 lb-in
Recommended Run in-lb	

General

Plated	N
Material - Hardware	Aluminum Alloy
UPC	781810159101
Material	Aluminum Alloy, Cast
Plating Type	Unplated
UPC 12 Digit	781810159101
UPC 14 Digit GTIN	00781810159101

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)