

# 2" Full Port Ball Valves "Stubby Valve"™

PATENTED

### FEATURES

- Stainless steel bolts.
- 100% PTFE ball seats.
- Glass-filled polypropylene.
- FKM (viton type) body seals.
- Unique compact design.
- 100 P.S.I. @ 70°F and 75 P.S.I. @ 150°F.
- Lightweight.

VSMT204FP



VSF204FP




VS204FP



VSFMT204FP



VSFMT204HSFP



| 2" FULL PORT STUBBY VALVES |  |         |           |                   |        |          |
|----------------------------|--|---------|-----------|-------------------|--------|----------|
| PART NO                    | DESCRIPTION  | MAX PSI | PIPE SIZE | OPENING THRU BALL | QTY    | PRICE    |
| VSMT204FP                  | 2" Male NPT x 2" Female NPT                                | 100     | 2"        | 2"                | 18/box | \$72.56  |
| VSF204FP                   | 2" Male Adapter x 2" Female NPT                            | 100     | 2"        | 2"                | 18/box | \$72.56  |
| VS204FP                    | 2" Female NPT x 2" Female NPT                              | 100     | 2"        | 2"                | 18/box | \$72.56  |
| VSFMT204FP                 | 2" Male Adapter x 2" Male NPT                              | 100     | 2"        | 2"                | 18/box | \$72.56  |
| VSFMT204HSFP               | 2" FP Male Adapter x 2" Male NPT w/ SS Ball, Stem & Handle | 100     | 2"        | 2"                | 18/box | \$190.50 |

| DIMENSION CHART IN INCHES (REFER TO DRAWING ABOVE) |   |      |      |      |
|--|---|------|------|------|
| PART NO  | DESCRIPTION   | A    | B    | C    |
| VSMT204FP  | 2" Male NPT x 2" Female NPT                             | 6.38 | 5.72 | 4.25 |
| VSMT204HSFP  | 2" Male Adapter x 2" Male NPT w/ SS Ball, Stem & handle | 5.94 | 6.50 | 4.25 |
| VSF204FP   | 2" Male Adapter x 2" Female NPT                         | 6.38 | 5.91 | 4.25 |
| VS204FP  | 2" Female NPT x 2" Female NPT                           | 6.38 | 5.19 | 4.25 |
| VSFMT204FP   | 2" Male Adapter x 2" Male NPT                           | 6.38 | 6.50 | 4.25 |

