


IPC13A & IPC13AT In Pan Condensate

FOR 115V, 60Hz


Beckett's IPC13A is a totally submersible pump with a built-in, hermetically sealed, pressure activated switch. The pump operates automatically when the water level reaches approximately 1.6 in. and turns off at 1.3 in. Because it is a totally submersible this pump may be used in ANY application where automatic control and dependability are required. The compact size, along with high lift and quiet operation of the IPC13A are well suited for a whole range of consumer and O.E.M. requirements, including condensation removal.



IPC13A



IPC13AT



Tank Capacity:
2.0 US quart (1.9 liters)

Model #	H	W	L	Outlet	Volts	Amps	Watts	Gallons per hour @ 115V, 60Hz				Shut Off (Ft.)	Weight Lb. Each	Safety Switch	Check Valve	6 Ft. Cord w/plug	Clear Tubing 20' 3/8"	cULus
								1'	5'	10'	15'							
IPC13A	4"	3 1/8"	8"	3/8" O.D.	115	0.9	55	80	70	45	-	12'	4.6		✓	✓		✓
IPC13AT	4.1"	5"	10.1"	3/8" O.D.	115	0.9	55	80	70	45	-	12'	6.3	✓	✓	✓	✓	✓

Average Performance