



AYPO300, Compression Pin Adapter, 300 kcmil, AL9CU

By Burndy
Catalog # [AYPO300](#)

300 kcmil, Aluminum Termination, Offset Pin, .53" Pin Dia, 1.34" Pin Length



Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	300 KCMIL
Conductor - AL Str Size	300 KCMIL
Conductor - AL Str Size Range	300 kcmil
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Flex I Size Range	250 kcmil
Conductor - Copper DLO Size Range	262 kcmil
Conductor - Copper Str Compact Size	300 KCMIL
Conductor - Copper DLO Size	262 KCMIL
Conductor Size	300 KCMIL
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	300 kcmil
Conductor - Copper Flex I Size	300 KCMIL

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	OFFSET PIN

Current

Voltage Rating	35 kV
Voltage - Maximum	35000 V

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	1.34 in
Dimension - L Length Overall mm	78 mm
Width	1.1 in
Dimension - A Outside	1.10 in
Diameter inch	
Dimension - Strip Length inch	1-1/8 in
Equivalent Pin Size	4/0 AWG
Length	3.08 in
Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.07 in

Dimension - B Outside	0.53 in
Diameter inch	
Height	1.1 in
Dimension - Length Overall	3.08 in
inch	
Dimensions	3.08 in x 1.1 in x 1.1 in

General

Insulation Type	Rubber
Trade Name	HYPLUG™
Die Index	299
Insulation	Y
Terminal Type	Pin
Plated	Y
Color Code	Brown
Pin Type	Solid
Sub Brand	HYPLUG

UPC	781810738429
Type	Aluminum Pin Adapters
Material	ALUMINUM
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810738429
UPC 14 Digit GTIN	00781810738429

Logistics

Pallet Quantity	2960
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand