

L-VLE, B-VLE series

**Pressed steel castors, medium-duty version,
with top plate, heavy-duty wheel
with super-elastic solid rubber tyres**



450 kg

Bracket: L/B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Swivel bracket:

- double ball bearing in the swivel head
- strong central kingpin
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process


Wheel: VLE series

- tyre: super-elastic solid rubber, hardness 70 Shore A, colour black, 2-component tyre, highly-elastic, abrasion-resistant tread
- rim: heavy pressed steel, zinc-plated, blue-passivated, Cr6-free

Additional details:

- bracket series: page 91
- brakes: page 112–113
- wheel series: page 249
- bearing types: page 84–85

4



Swivel castors	Fixed castors	Swivel castor with "stop-top" brake	Wheel Ø [mm]	Tyre width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate size [mm]	Bolt hole spacing [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]	Profile type
L-VLE 250K	B-VLE 250K	L-VLE 250K-ST	250	85	450	ball bearing	295	175 x 175	140 x 140	15	70	R50
L-VLE 255K		L-VLE 255K-ST	250	85	450	ball bearing	295	220 x 130	190 x 75	15	–	R50
	B-VLE 255K		250	85	450	ball bearing	295	175 x 175	140 x 140	15	70	B51
				250	85	450	ball bearing	295	220 x 130	190 x 75	15	–

Profile types: R = ribbed profile, B = zig-zag profile, see page 252 for image

Versions / options



	with non-marking grey tyre	antistatic version, black tyres
Technical description page	52	50
Product code suffix	-SG	-AS
Available for	upon request	upon request