


Series: LER-POW

**Pressed steel castors with bolt hole fitting, with noise absorbing nylon wheel**

150 kg

RoHS



**Brackets:** LER series - Made of pressed steel, with double ball bearing in the swivel head, strong central kingpin, ball protection by the special top plate and ball disc design. The special Blickle dynamic riveting process of the swivel head results in minimal swivel head play and smooth rolling characteristics with an increased service life achieved by the work hardening of the ball race grooves. Bolted wheel axle. Zinc-plated, blue-passivated, Cr6-free. Bracket overview: Page 65

**Wheels:** POW series - Made of high-quality, impact-resistant nylon, 70° shore D, white, with elastic solid rubber damping ring, red. Bearing types: Roller bearing or a centrally encapsulated ball bearing (C), both with synthetic thread guard. Detailed description: Page 288 and 49

Wheel and swivel head 'stop-fix' brake: Page 80

Swivel castors	Swivel castors with 'stop-fix' brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate Ø [mm]	Bolt hole Ø [mm]	Offset [mm]
LER-POW 100R-FK	LER-POW 100R-FI-FK	100	35	150	Roller bearing	125	70	13	36
LER-POW 100K-FK	LER-POW 100K-FI-FK	100	35	150	Ball bearing (C)	125	70	13	36
LER-POW 125R-FK	LER-POW 125R-FI-FK	125	35	150	Roller bearing	150	70	13	40
LER-POW 125K-FK	LER-POW 125K-FI-FK	125	35	150	Ball bearing (C)	150	70	13	40

For stainless steel versions refer to page 374

13

**Options**



	With synthetic foot guard	With stainless steel roller bearing in the wheel hub	Wheel with additional ball bearing seals
Technical description page	84	60	61
Product code suffix	-FP	-XR	-KD
Available for	wheel Ø 125 mm upon request	upon request	upon request