



BA10E6M, Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

By Burndy
Catalog # [BA10E6M](#)



Vinyl Ring Terminal For 12 - 10 AWG (Tape Mounted)

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	12 AWG 10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
--------------------------------------	---

Connector Type	Ring Terminal
Dimensions	
Dimension - Z inch	0.20 in
Dimension - Pad Width inch	0.31 in
Length	0.91 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.15 in
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	0.91 in
Width	0.3 in
Height	0.3 in
Dimensions	0.91 in x 0.3 in x 0.3 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
Type	Ring Tongue
UPC 12 Digit	781810028841
UPC 14 Digit GTIN	00781810028841
Material	Copper
Plating Type	Tin - Electro Plated
UPC	781810028841

Logistics

Minimum Pack Quantity	1000
-----------------------	------

Product Assets

[Catalog \[English\]](#)