



BA14E10M, Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

By Burndy
Catalog # [BA14E10M](#)



Vinyl Ring Terminal For 16 - 14 AWG (Tape Mounted)

Features

- Vinyl Ring Terminal banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.31 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Bolt Size fraction	#10
Length	0.85 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.26 in
Height	0.32 in
Width	0.32 in
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.85 in
Dimension - Stud Size inch	#10
Dimensions	0.85 in x 0.32 in x 0.32 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Ring
UPC	781810028964
Type	Ring Tongue
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810028964
UPC 14 Digit GTIN	00781810028964

Product Assets

[Catalog \[English\]](#)