



BA14E38, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [BA14E38](#)



Vinyl Ring Terminal For 16 - 14 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor - Copper Solid Size	16 AWG 15 AWG 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor - Copper Str Size	16 AWG 14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Dimension - Hole Size fraction	16/41 in
Dimension - Bolt Size fraction	3/8
Length	1.15 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.45 in
Height	0.54 in
Width	0.54 in
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	1.15 in
Dimension - Stud Size inch	3/8 in
Dimensions	1.15 in x 0.54 in x 0.54 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Ring
UPC	781810091500
Type	Ring Tongue
Insulation	Y
Material	Copper
Plating Type	Tin - Electroplated

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)