

LKR-ALTH series

Pressed steel castors, heavy-duty design, with bolt hole, wheel with Blickle Extrathane® polyurethane tread



200–350 kg

Bracket: LKR series


- strong pressed steel, zinc-plated, blue-passivated, Cr6-free
- double ball bearing in the swivel head
- strong central kingpin
- minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process

Wheel: ALTH series

- tread: high-quality polyurethane elastomer Blickle Extrathane®, hardness 92 Shore A, colour light brown, non-marking, non-staining
- wheel centre: die-cast aluminium, colour silver grey

Additional details:

- bracket series: page 92
- brakes: page 112–113
- wheel series: page 274
- bearing types: page 84–85



5

Swivel castors	Swivel castors with "stop-fix" brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate Ø [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]
LKR-ALTH 80K	LKR-ALTH 80K-FI	80	30	200	ball bearing	110	88	13	40
LKR-ALTH 100K	LKR-ALTH 100K-FI	100	40	350	ball bearing	130	88	13	45
LKR-ALTH 125K	LKR-ALTH 125K-FI	125	40	350	ball bearing	155	88	13	48
LKR-ALTH 125K-CO	LKR-ALTH 125K-FI-CO	125	40	350	ball bearing	155	88	13	48

Versions / options



	version with extremely crowned tread	antistatic version, non-marking grey	truck lock
Technical description page	55	50	114
Product code suffix	-CO	-AS	FF 100-1 / FF 125-1
Available for		all	wheel Ø 100+125 mm