



BA16E38, Vinyl Ring Terminal For 22 - 16 AWG

By Burndy
Catalog # [BA16E38](#)



Vinyl Ring Terminal For 22 - 16 AWG

Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serration in the inner barrel for added holding strength and better conductivity
- Electro-tin plating for durable, long-lasting corrosion resistance
- 600 Volts maximum, 105°C maximum

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Industry Standard(s)	UL467
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size Range	20 AWG -22 AWG 16 AWG -18 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size Range	20 AWG - 22 AWG 16 AWG - 18 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.45 in
Dimension - Pad Width inch	0.53 in
Package Height	0.000 in
Length	1.15 in
Dimension - Hole Size fraction	16/41
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.39 in
Dimension - Stud Size inch	3/8
Dimension - Length Overall inch	1.15 in
Width	0.54 in
Height	0.54 in
Dimensions	1.15 in x 0.54 in x 0.54 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Ring
Trade Name	VINYLUG™
Plated	Y
Feature - Barrel Style	Shrouded
Insulation Type	Y
Type	Ring Tongue
UPC 12 Digit	781810026724
UPC 14 Digit GTIN	00781810026724
Material	Copper
Plating Type	Tin
UPC	781810026724

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)