

## LRXA-TPA, BRXA-TPA, LKRXA-TPA, BKRXA-TPA series


### Stainless steel light-duty castors with bolt hole, wheel with thermoplastic rubber tread

50–120 kg

- Bracket:** LRXA/BRXA, LKRXA/BKRXA series
- high-quality chromium-nickel steel (1.4301/ AISI 304), stainless steel, vibration-ground finishing
  - all parts including axle material are corrosion-resistant
- swivel bracket:**
- double ball bearing in the swivel head
  - strong central kingpin
  - minimum swivel head play and smooth rolling characteristic and increased service life due to the special dynamic Blickle riveting process
  - synthetic “stop-fix” brake lever for series LRXA, steel brake lever for series LKRXA

- Wheel:** TPA series
- tread: high-quality thermoplastic rubber-elastomer (TPE), hardness 85 Shore A, colour grey, non-marking, oil containing
  - wheel centre: high-quality polypropylene, impact resistant, colour silver grey (“-ELS” version colour black)

- Additional details:**
- bracket series: page 95
  - brakes: page 112–113
  - wheel series: page 60
  - bearing types: page 84–85



Swivel castors	Fixed castors	Swivel castors with “stop-fix” brake	Wheel Ø [mm]	Wheel width [mm]	Load capacity [kg]	Bearing type	Total height [mm]	Plate Ø [mm]	Bolt hole Ø [mm]	Offset swivel castor [mm]
LRXA-TPA 50G	BRXA-TPA 50G	LRXA-TPA 50G-FI	50	19	50	plain bore	69	43	11	23
LRXA-TPA 50KFD	BRXA-TPA 50KFD	LRXA-TPA 50KFD-FI	50	19	50	ball bearing (C)	69	43	11	23
LRXA-TPA 75G	BRXA-TPA 75G	LRXA-TPA 75G-FI	75	25	75	plain bore	98	43	11	29
LRXA-TPA 75KFD	BRXA-TPA 75KFD	LRXA-TPA 75KFD-FI	75	25	75	ball bearing (C)	98	43	11	29
LKRXA-TPA 80G	BKRXA-TPA 80G	LKRXA-TPA 80G-FI	80	32	100	plain bore	108	57	13	40
LKRXA-TPA 80G-11		LKRXA-TPA 80G-11-FI	80	32	100	plain bore	108	57	11	40
LKRXA-TPA 80KFD	BKRXA-TPA 80KFD	LKRXA-TPA 80KFD-FI	80	32	100	ball bearing (C)	108	57	13	40
LKRXA-TPA 80KFD-11		LKRXA-TPA 80KFD-11-FI	80	32	100	ball bearing (C)	108	57	11	40
LKRXA-TPA 101G	BKRXA-TPA 101G	LKRXA-TPA 101G-FI	100	32	110	plain bore	133	57	13	40
LKRXA-TPA 101G-11		LKRXA-TPA 101G-11-FI	100	32	110	plain bore	133	57	11	40
LKRXA-TPA 101KFD	BKRXA-TPA 101KFD	LKRXA-TPA 101KFD-FI	100	32	110	ball bearing (C)	133	57	13	40
LKRXA-TPA 101KFD-11		LKRXA-TPA 101KFD-11-FI	100	32	110	ball bearing (C)	133	57	11	40
LKRXA-TPA 126G	BKRXA-TPA 126G	LKRXA-TPA 126G-FI	125	32	120	plain bore	158	57	13	40
LKRXA-TPA 126G-11		LKRXA-TPA 126G-11-FI	125	32	120	plain bore	158	57	11	40
LKRXA-TPA 126KFD	BKRXA-TPA 126KFD	LKRXA-TPA 126KFD-FI	125	32	120	ball bearing (C)	158	57	13	40
LKRXA-TPA 126KFD-11		LKRXA-TPA 126KFD-11-FI	125	32	120	ball bearing (C)	158	57	11	40

8

### Versions / options



	plain bore version	illustration with plastic brake pedal, colour black	illustration with plastic brake pedal, colour grey	electrically conductive version, non-marking grey	with synthetic expander fitting, corrosion-resistant	with plug-in stem made of stainless steel	buffers
Technical description page				50	105	104	116
Product code suffix				-ELS	see page 398	see page 398	AG / ARG series
Available for		series LRXA...-FI as standard	series LKRXA...-FI as standard	all*	swivel castors with bolt hole Ø 11 mm (except ELS)	swivel castors with wheel Ø 125 mm and bolt hole Ø 13 mm**	see page 398

\* Wheel load capacity of electrically conductive version reduced by 35%  
 \*\* In accordance with DIN 18867-8 (large-scale catering equipment)