



BA16E6M, Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted)

By Burndy
Catalog # [BA16E6M](#)

Vinyl Ring Terminal For 22 - 16 AWG (Tape Mounted)



Features

- Vinyl Ring Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size Range	• 20 AWG -22 AWG • 16 AWG -18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	• 20 AWG - 22 AWG • 16 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Dimension - Pad Width inch	0.25 in
Package Height	0.000 in
Dimension - Hole Size fraction	3/20
Dimension - Bolt Size fraction	#6
Length	0.74 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.18 in
Height	0.26 in
Width	0.26 in
Dimension - Hole Size inch	0.15 in
Dimension - Length Overall inch	0.74 in
Dimension - Stud Size inch	#6
Dimensions	0.74 in x 0.26 in x 0.26 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Insulation Type	Vinyl
Trade Name	VINYLUG™
Physical Attribute - Tongue Type	Ring
UPC	781810029060
Type	Ring Tongue
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810029060
UPC 14 Digit GTIN	00781810029060

Product Assets

[Catalog \[English\]](#)