



BA16EF10, Vinyl Fork Terminal For 22 - 16 AWG

By Burndy
Catalog # [BA16EF10](#)

Vinyl Fork Terminal For 22 - 16 AWG



Features

- Fork terminals are constructed of pure electrolytic copper
- Long brazed seam barrel with deep V groove inner serrations for optimum conductivity, reliability and holding power after crimping
- Fork tongue design for faster installation - screw only needs to be loosened for termination
- Two or more terminals can be stacked on a common stud
- Provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating for durable, long lasting corrosion resistance
- Inspection hole/skive provides an easy visual check of proper wire insertion
- 600 Volts maximum, 105°C maximum

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	22 - 16 AWG
Conductor - Copper Solid Size Range	• 20 AWG -22 AWG • 16 AWG -18 AWG
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	• 20 AWG - 22 AWG • 16 AWG - 18 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Fork Terminal

Dimensions

Dimension - Pad Width inch	0.41 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Width	0.41 in
Dimension - Hole Size inch	0.20 in
Dimension - Stud Size inch	#10
Dimension - Bolt Size fraction	#10
Length	0.95 in
Dimension - Z inch	0.31 in
Height	0.41 in
Dimension - Length Overall inch	0.95 in
Dimensions	0.95 in x 0.41 in x 0.41 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Physical Attribute - Tongue Type	Fork
Sub Brand	VINYLUG
UPC	781810026762
Type	BA-EF
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810026762
UPC 14 Digit GTIN	00781810026762

Logistics

Pallet Quantity	99999
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)

