




TYPE 2




TYPE 4




TYPE 5




TYPE 6




TYPE 7




TYPE 13



TYPE 16



TYPE 17



TYPE 18

BORE RANGE

TABLE No. 1

BORE RANGE	BUSHING
3/8" to 1"	G
3/8 to 1 1/2	H
1/2 to 1 3/4	P1

STANDARD KEYSEATS

TABLE No. 2

BORE RANGE	KEYSEATS
3/8" & 7/16"	None
1/2 & 9/16	1/8" x 1/16"
5/8 to 7/8	3/16 x 3/32
15/16 to 1 1/4	1/4 x 1/8
1 5/16 & 1 3/8	5/16 x 5/32
1 7/16 to 1 3/4	3/8 x 3/16

1 3/8" Bore Bushings also available with 3/8" x 7/16" Keyseat.

TABLE No. 3

SPECIFICATIONS-STOCK MINIMUM BORE GEARBELT® PULLEYS

PART NUMBER	DIAMETERS			NUMBER OF GROOVES	TYPE	BORE		DIMENSIONS				WT. Lbs.
	PITCH	OUTSIDE	FLANGE			STOCK	MAX.	F	L	P	H	
FOR L050 BELTS, 3/8" PITCH, 1/2" WIDE												
18LB050	2.149"	2.119"	2 7/16"	18	2	1/2"	7/8"	3/4"	1 1/4"	1/2"	1 9/16	.8
19LB050	2.268	2.238	2 5/8	19	2	1/2	7/8	3/4	1 1/4	1/2	1 11/16	.9
20LB050	2.387	2.357	2 5/8	20	2	1/2	7/8	3/4	1 1/4	1/2	1 11/16	1.0
21LB050	2.507	2.477	2 7/8	21	2	1/2	1 1/4	3/4	1 1/4	1/2	2	1.3
22LB050	2.626	2.596	2 7/8	22	2	1/2	1 1/4	3/4	1 1/4	1/2	2	1.4
24LB050	2.865	2.835	3 1/8	24	2	1/2	1 3/8	3/4	1 1/4	1/2	2 1/4	1.8
26LB050	3.104	3.074	3 3/8	26	2	1/2	1 3/8	3/4	1 1/4	1/2	2 1/4	2.1
28LB050	3.342	3.312	3 5/8	28	2	1/2	1 3/8	3/4	1 1/4	1/2	2 1/4	2.3
30LB050	3.581	3.551	3 13/16	30	2	1/2	1 3/8	3/4	1 1/4	1/2	2 1/4	2.4
32LB050	3.820	3.790	4 1/16	32	2	1/2	1 5/8	3/4	1 1/4	1/2	2 5/8	3.0
36LB050	4.297	4.267	4 11/16	36	2	1/2	2 5/16	3/4	1 1/4	1/2	3 1/2	3.8
40LB050	4.775	4.745	5	40	2	1/2	2 3/8	3/4	1 1/4	1/2	3 5/8	4.6
FOR L075 BELTS, 3/8" PITCH, 3/4" WIDE												
18LB075	2.149"	2.119"	2 7/16"	18	2	1/2"	7/8"	1"	1 1/2"	1/2"	1 9/16	1.0
19LB075	2.268	2.238	2 5/8	19	2	1/2	7/8	1	1 1/2	1/2	1 11/16	1.3
20LB075	2.387	2.357	2 5/8	20	2	1/2	7/8	1	1 1/2	1/2	1 11/16	1.3
21LB075	2.507	2.477	2 7/8	21	2	5/8	1 1/4	1	1 1/2	1/2	2	1.6
22LB075	2.626	2.596	2 7/8	22	2	5/8	1 1/4	1	1 1/2	1/2	2	1.8
24LB075	2.865	2.835	3 1/8	24	2	5/8	1 3/8	1	1 1/2	1/2	2 1/4	2.1
26LB075	3.104	3.074	3 3/8	26	2	5/8	1 3/8	1	1 1/2	1/2	2 1/4	2.4
28LB075	3.342	3.312	3 5/8	28	2	5/8	1 3/8	1	1 1/2	1/2	2 1/4	2.9
30LB075	3.581	3.551	3 13/16	30	2	5/8	1 3/8	1	1 1/2	1/2	2 1/4	3.0
32LB075	3.820	3.790	4 1/16	32	2	5/8	1 5/8	1	1 1/2	1/2	2 5/8	3.6
36LB075	4.297	4.267	4 11/16	36	2	5/8	2 5/16	1	1 1/2	1/2	3 1/2	4.4
40LB075	4.775	4.745	5	40	2	5/8	2 3/8	1	1 1/2	1/2	3 5/8	5.0
FOR L100 BELTS, 3/8" PITCH, 1" WIDE												
18LB100	2.149"	2.119"	2 7/16"	18	2	1/2"	7/8"	1 1/4"	1 3/4"	1/2"	1 9/16	1.2
19LB100	2.268	2.238	2 5/8	19	2	1/2	7/8	1 1/4	1 3/4	1/2	1 11/16	1.4
20LB100	2.387	2.357	2 5/8	20	2	1/2	7/8	1 1/4	1 3/4	1/2	1 11/16	1.8
21LB100	2.507	2.477	2 7/8	21	2	5/8	1 1/4	1 1/4	1 3/4	1/2	2	2.0
22LB100	2.626	2.596	2 7/8	22	2	5/8	1 1/4	1 1/4	1 3/4	1/2	2	2.1
24LB100	2.865	2.835	3 1/8	24	2	5/8	1 3/8	1 1/4	1 3/4	1/2	2 1/4	2.5
26LB100	3.104	3.074	3 3/8	26	2	5/8	1 5/8	1 1/4	1 3/4	1/2	2 7/16	3.0
28LB100	3.342	3.312	3 5/8	28	2	5/8	1 3/4	1 1/4	1 3/4	1/2	2 11/16	3.6
30LB100	3.581	3.551	3 13/16	30	2	5/8	1 7/8	1 1/4	1 3/4	1/2	2 13/16	4.1
32LB100	3.820	3.790	4 1/16	32	2	5/8	2	1 1/4	1 3/4	1/2	3 1/8	4.8
36LB100	4.297	4.267	4 11/16	36	2	5/8	2 5/16	1 1/4	1 3/4	1/2	3 1/2	5.4
40LB100	4.775	4.745	5	40	2	5/8	2 5/16	1 1/4	1 3/4	1/2	3 5/8	6.0

Browning® Stock Minimum Bore Pulleys for "L" Gearbelt belts are furnished without keyseats or setscrews. They can be bored to size and furnished with keyseats and setscrews at a reasonable extra price.

Maximum Bores shown will accommodate Standard Keyseats and Setscrew over Keyseat. Slightly Larger Bores are possible without Ks., Shallow Ks. or Setcrew at angle to Ks.

TABLE No. 1 SPECIFICATIONS STOCK GEARBELT® PULLEYS WITH BROWNING SPLIT TAPER® BUSHINGS

PART NUMBER		DIAMETERS				NUMBER OF GROOVES	TYPE	DIMENSIONS									WT. Lbs. LESS BUSH
PULLEY	BUSHING	PITCH	OUTSIDE	INSIDE	FLANGE			O.L.	F	L	P	C	H	G	X	E	
FOR L050 BELTS, 3/8" PITCH, 1/2" WIDE																	
18LG050	G	2.149"	2.119"	-	2 7/16"	18	4	1 3/8"	3/4"	1"	7/16"	3/16"	2"	-	-	3/16"	.5
19LG050	G	2.268	2.238	-	2 5/8"	19	4	1 3/8"	3/4"	1	7/16"	3/16"	2	-	-	3/16"	.5
20LG050	G	2.387	2.357	-	2 5/8"	20	4	1 3/8"	3/4"	1	7/16"	3/16"	2	-	-	3/16"	.6
21LG050	G	2.507	2.477	-	2 7/8"	21	4	1 3/8"	3/4"	1	7/16"	3/16"	2	-	-	3/16"	.7
22LG050	G	2.626	2.596	-	2 7/8"	22	4	1 3/8"	3/4"	1	7/16"	3/16"	2	-	-	3/16"	.8
24LH050	H	2.865	2.835	-	3 1/8"	24	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	1.0
26LH050	H	3.104	3.074	-	3 3/8"	26	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	1.0
28LH050	H	3.342	3.312	-	3 5/8"	28	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	1.4
30LH050	H	3.581	3.551	-	3 13/16"	30	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	1.9
32LH050	H	3.820	3.790	-	4 1/16"	32	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	2.0
36LH050	H	4.297	4.267	-	4 11/16"	36	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	2.5
36LP050	P1	4.297	4.267	-	4 11/16"	36	7	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	2.8
40LH050	H	4.775	4.745	-	5	40	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	3.5
40LP050	P1	4.775	4.745	-	5	40	7	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	3.4
44LH050	H	5.252	5.222	-	5 1/2"	44	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	4.0
44LP050	P1	5.252	5.222	-	5 1/2"	44	7	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	4.1
48LH050	H	5.730	5.700	-	6	48	5	1 7/16"	3/4"	1 1/4"	7/16"	1/16"	2 1/2"	-	-	3/16"	4.9
48LP050	P1	5.730	5.700	-	6	48	7	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	4.9
60LH050	H	7.162	7.132	6 7/16"	-	60	17	1 1/2"	3/4"	1 1/4"	7/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	4.3
60LP050	P1	7.162	7.132	6 7/16"	-	60	13	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	4.9
72LH050	H	8.594	8.564	7 13/16"	-	72	17	1 1/2"	3/4"	1 1/4"	7/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	5.3
72LP050	P1	8.594	8.564	7 13/16"	-	72	13	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	6.0
84LH050	H	10.027	9.997	9 1/4"	-	84	17	1 1/2"	3/4"	1 1/4"	7/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	6.2
84LP050	P1	10.027	9.997	9 1/4"	-	84	13	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	7.0
96LH050	H	11.459	11.429	10 11/16"	-	96	17	1 1/2"	3/4"	1 1/4"	7/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	7.3
96LP050	P1	11.459	11.429	10 11/16"	-	96	13	2 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	8.5
120LH050	H	14.324	14.294	13 9/16"	-	120	17	1 1/2"	3/4"	1 1/4"	7/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	9.5
120LP050	P1	14.324	14.294	13 9/16"	-	120	13	3 3/16"	3/4"	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	10.8
FOR L075 BELTS, 3/8" PITCH, 3/4" WIDE																	
18LG075	G	2.149"	2.119"	-	2 7/16"	18	4	1 5/8"	1"	1"	7/16"	7/16"	2"	-	-	3/16"	.6
19LG075	G	2.268	2.238	-	2 5/8"	19	4	1 5/8"	1	1	7/16"	7/16"	2	-	-	3/16"	.8
20LG075	G	2.387	2.357	-	2 5/8"	20	4	1 5/8"	1	1	7/16"	7/16"	2	-	-	3/16"	.8
21LG075	G	2.507	2.477	-	2 7/8"	21	4	1 5/8"	1	1	7/16"	7/16"	2	-	-	3/16"	1.0
22LG075	G	2.626	2.596	-	2 7/8"	22	4	1 5/8"	1	1	7/16"	7/16"	2	-	-	3/16"	1.1
24LH075	H	2.865	2.835	-	3 1/8"	24	4	1 5/8"	1	1 1/4"	7/16"	3/16"	2 1/2"	-	-	3/16"	1.1
26LH075	H	3.104	3.074	-	3 3/8"	26	4	1 5/8"	1	1 1/4"	7/16"	3/16"	2 1/2"	-	-	3/16"	1.5
28LH075	H	3.342	3.312	-	3 5/8"	28	4	1 5/8"	1	1 1/4"	7/16"	3/16"	2 1/2"	-	-	3/16"	1.8
30LH075	H	3.581	3.551	-	3 13/16"	30	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	1.9
32LH075	H	3.820	3.790	-	4 1/16"	32	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	2.3
36LH075	H	4.297	4.267	-	4 11/16"	36	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	3.0
36LP075	P1	4.297	4.267	-	4 11/16"	36	7	2 3/16"	1	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	3.9
40LH075	H	4.775	4.745	-	5	40	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	3.8
40LP075	P1	4.775	4.745	-	5	40	7	2 3/16"	1	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	3.9
44LH075	H	5.252	5.222	-	5 1/2"	44	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	4.9
44LP075	P1	5.252	5.222	-	5 1/2"	44	7	2 3/16"	1	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	4.9
48LH075	H	5.730	5.700	-	6	48	16	1 7/16"	1	1 1/4"	1/4"	0	2 1/2"	7/16"	13/16"	3/16"	5.8
48LP075	P1	5.730	5.700	-	6	48	7	2 3/16"	1	1 15/16"	5/8"	9/16"	3	-	1 5/16"	1/4"	5.9
60LH075	H	7.162	7.132	6 7/16"	-	60	17	1 1/2"	1	1 1/4"	5/16"	1/16"	2 1/2"	7/16"	7/8"	3/16"	4.6
60LP075	P1	7.162	7.132	6 7/16"	-	60	13	2 3/16"	1	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	5.3
72LH075	H	8.594	8.564	7 13/16"	-	72	17	1 1/2"	1	1 1/4"	5/16"	1/16"	2 1/2"	7/16"	7/8"	3/16"	5.6
72LP075	P1	8.594	8.564	7 13/16"	-	72	13	2 3/16"	1	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	6.6
84LH075	H	10.027	9.997	9 1/4"	-	84	17	1 1/2"	1	1 1/4"	5/16"	1/16"	2 1/2"	7/16"	7/8"	3/16"	6.7
84LP075	P1	10.027	9.997	9 1/4"	-	84	13	2 3/16"	1	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	7.5
96LH075	H	11.459	11.429	10 11/16"	-	96	17	1 1/2"	1	1 1/4"	5/16"	1/16"	2 1/2"	7/16"	7/8"	3/16"	7.9
96LP075	P1	11.459	11.429	10 11/16"	-	96	13	2 3/16"	1	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	8.8
120LH075	H	14.324	14.294	13 9/16"	-	120	17	1 1/2"	1	1 1/4"	5/16"	1/16"	2 1/2"	7/16"	7/8"	3/16"	10.4
120LP075	P1	14.324	14.294	13 9/16"	-	120	13	2 3/16"	1	1 15/16"	5/8"	9/16"	3	7/16"	1 9/16"	1/4"	11.4
FOR L100 BELTS, 3/8" PITCH, 1" WIDE																	
18LG100	G	2.149"	2.119"	-	2 7/16"	18	4	1 7/8"	1 1/4"	1"	7/16"	11/16"	2"	-	-	3/16"	.8
19LG100	G	2.268	2.238	-	2 5/8"	19	4	1 7/8"	1 1/4"	1	7/16"	11/16"	2	-	-	3/16"	1.0
20LG100	G	2.387	2.357	-	2 5/8"	20	4	1 7/8"	1 1/4"	1	7/16"	11/16"	2	-	-	3/16"	1.1
21LG100	G	2.507	2.477	-	2 7/8"	21	4	1 7/8"	1 1/4"	1	7/16"	11/16"	2	-	-	3/16"	1.3
22LG100	G	2.626	2.596	-	2 7/8"	22	4	1 7/8"	1 1/4"	1	7/16"	11/16"	2	-	-	3/16"	1.5
24LH100	H	2.865	2.835	-	3 1/8"	24	4	1 7/8"	1 1/4"	1 1/4"	7/16"	7/16"	2 1/2"	-	-	3/16"	1.5
26LH100	H	3.104	3.074	-	3 3/8"	26	4	1 7/8"	1 1/4"	1 1/4"	7/16"	7/16"	2 1/2"	-	-	3/16"	1.9
28LH100	H	3.342	3.312	-	3 5/8"	28	4	1 7/8"	1 1/4"	1 1/4"	7/16"	7/16"	2 1/2"	-	-	3/16"	2.3
30LH100	H	3.581	3.551	-	3 13/16"	30	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	2.3
32LH100	H	3.820	3.790	-	4 1/16"	32	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	2.7
36LH100	H	4.297	4.267	-	4 11/16"	36	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	3.2
36LP100	P1	4.297	4.267	-	4 11/16"	36	6	2 3/16"	1 1/4"	1 15/16"	5/8"	1/16"	3	-	13/16"	1/4"	3.9
40LH100	H	4.775	4.745	-	5	40	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	4.0
40LP100	P1	4.775	4.745	-	5	40	6	2 3/16"	1 1/4"	1 15/16"	5/8"	1/16"	3	-	13/16"	1/4"	5.0
44LH100	H	5.252	5.222	-	5 1/2"	44	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	4.9
44LP100	P1	5.252	5.222	-	5 1/2"	44	6	2 3/16"	1 1/4"	1 15/16"	5/8"	1/16"	3	-	13/16"	1/4"	6.3
48LH100	H	5.730	5.700	-	6	48	16	1 7/16"	1 1/4"	1 1/4"	0	0	2 1/2"	7/16"	13/16"	3/16"	6.2
48LP100	P1	5.730	5.700	-	6	48	6	2 3/16"	1 1/4"	1 15/16"	5/8"	1/16"	3	-	13/16"	1/4"	7.8
60LH100	H	7.162	7.132	6 7/16"	-	60	18	1 1/2"	1 1/4"	1 1/4"	1/16"	1/8"	2 1/2"	7/16"	7/8"	3/16"	5.1
60LP100	P1	7.162	7.132	6 7/16"	-	60	13	2 3/16"	1 1/4"	1 15/16"	5/8"	1/16"	3	7/16"	1 9/16"	1/4"	5.9
72LH100	H	8.594	8.564	7 13/16"													