



BDALHC212500, Power Distribution Block Adder

By Burndy
Catalog # [BDALHC212500](#)

Distribution Block, High Conductive Al Body & Gas Filled Polycarbonate Insulator, #4 AWG- 500 kcmil (Run), #14 - #4 AWG (Tap), 760 Amps

Features

- VERSIPOLE Configurable Power Distribution Blocks
- Available in 3 sizes for optimization of space
- Suitable for use with aluminum or copper conductors
- Single or dual run connections
- 600V Al/Cu Rated
- High short-circuit rating up to 100kA with proper fusing
- Adders and end barriers available separate for all 3 sizes

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	4-500
Conductor - Copper Str Run	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0 • 250 • 300 • 350 • 400 • 450 • 500
Number Of Poles	Adder
Conductor - AL Str Run Range	4-500
Conductor - AL Str Run	• 4 • 3 • 2 • 1 • 1/0 • 2/0 • 3/0 • 4/0



Conductor - AL Str Tap Range	• 250 • 266.8 • 300 • 336.4 • 350 • 397.5 • 400 • 450 • 477 • 500
Conductor - AL Str Tap	12-4
Conductor - Copper Str Tap Range	• 12 • 10 • 8 • 6 • 5 • 4
Conductor - Copper Str Tap	14-4
Conductor - Copper Str Tap	• 14 • 12 • 10 • 9 • 8 • 7 • 6 • 5 • 4

Current

Amperage Rating	760 A
Rating - Minimum Voltage	600

Dimensions

Package Height	0.000 in
Dimension - Height mm	90.2 mm
Dimension - Height inch	3.55 in
Package Weight	0.000 lb.
Dimension - Width mm	66 mm
Dimension - Width inch	2.58 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	145 mm

Dimension - Length Overall inch	5.70 in
General	
Plated	N
Trade Name	VERSIPOLE™
UPC	781810645574
Insulation	Y
Material	Aluminum
Plating Type	Tin
UPC 12 Digit	781810645574
UPC 14 Digit GTIN	00781810645574

Logistics	
Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	18

Operational	
Temperature Rating	194° F

Product Assets
[Catalog \[English\]](#)



A Hubbell brand