

Browning® Stock Sprockets for Extended Pitch Chain have larger pitch diameters than standard roller chain sprockets as extended pitch chain will not operate satisfactorily on standard roller chain sprockets with less than 24 teeth. They will normally operate satisfactorily on standard roller chain sprockets with 24 or more teeth. Sprockets for Extended Pitch Chain with Large Rollers are available on special order.

**TABLE No. 1 STOCK SPROCKETS WITH BROWNING SPLIT TAPER® BUSHINGS FOR EXTENDED PITCH CHAIN WITH STANDARD ROLLERS**

**For No. 2040. 1" Extended Pitch Roller Chain**

PART No.	BUSHING	BORE RANGE	DIAMETER		No. OF TEETH,*	TYPE	T (NOM.)	O.L.	L	P	C	H	G	X	E	Wt. lbs. LESS BUSH.
			OUTSIDE	PITCH												
2040H17	H	3/8 - 1 1/2	2.96	2.768	17	3	.275	1 1/2	1 1/4	1 1/32	1/16	2 1/2	7/16	7/8	3/16	.6
2040H21	H	3/8 - 1 1/2	3.62	3.392	21	3	.275	1 1/2	1 1/4	1 1/32	1/16	2 1/2	7/16	7/8	3/16	.9

**For No.2050. 1 1/4" Extended Pitch Roller Chain**

2050H17	H	3/8 - 1 1/2	3.72	3.460	17	3	.343	1 1/2	1 1/4	31/32	1/16	2 1/2	7/16	7/8	3/16	1.0
2050P21	P1	1/2 - 1 3/4	4.52	4.241	21	4	.343	2 3/16	1 15/16	1 19/32	0	3	5/8	1 5/16	1/4	2.0
2050P23	P1	1/2 - 1 3/4	4.92	4.633	23	4	.343	2 3/16	1 15/16	1 19/32	0	3	5/8	1 5/16	1/4	2.4


**For No.2060. 1 1/2" Extended Pitch Roller Chain**

2060P17	P1	1/2 - 1 3/4	4.46	4.152	17	4	.459	2 3/16	1 15/16	1 15/32	0	3	5/8	1 5/16	1/4	2.2
2060P19	P1	1/2 - 1 3/4	4.95	4.620	19	4	.459	2 3/16	1 15/16	1 15/32	0	3	5/8	1 5/16	1/4	2.6
2060P23	P1	1/2 - 1 3/4	5.90	5.560	23	4	.459	2 3/16	1 15/16	1 15/32	0	3	5/8	1 5/16	1/4	3.5

**For No.2080. 2" Extended Pitch Roller Chain**

2080P17	P1	1/2 - 1 3/4	5.94	5.536	17	4	.575	2 3/16	1 15/16	1 3/8	0	3	5/8	1 5/16	1/4	3.9
2080Q19	Q1	3/4 - 2 11/16	6.59	6.160	19	4	.575	2 25/32	2 1/2	2 1/64	3/32	4 1/8	27/32	1 21/32	15/64	6.4
2080Q21	Q1	3/4 - 2 11/16	7.23	6.785	21	4	.575	2 25/32	2 1/2	2 1/64	3/32	4 1/8	27/32	1 21/32	15/64	7.4
2080Q23	Q1	3/4 - 2 11/16	7.87	7.413	23	4	.575	2 25/32	2 1/2	2 1/64	3/32	4 1/8	27/32	1 21/32	15/64	8.5

## HARDENED TEETH



## STANDARD KEYSEATS

TABLE No. 3

BORE RANGE	KEYSEAT
3/8" - 7/16"	None
1/2 - 9/16	1/8" X 1/16"
5/8 - 7/8	3/16 X 3/32
15/16 - 1 1/4	1/4 X 1/8
1 5/16 - 1 3/8	5/16 X 5/32
1 7/16 - 1 3/4	3/8 X 3/16
1 13/16 - 2 1/4	1/2 X 1/4
2 5/16 - 2 3/4	5/8 X 5/16

1 3/8" Bore Bushings also available with 3/8" x 7/16" Keyseat.